

Product data sheet

Specifications



capacitor bank - Varset Classic - 400/415V - 35kvar - step 7x5 enclosure C1

52853

⚠ Discontinued on: Dec 31, 2013

⚠ End-of-service on: Apr 30, 2021

⚠ Discontinued

Main

Range Of Product	VarSet
Device Short Name	Varset Classic
Product Or Component Type	Capacitor bank
Device Presentation	Enclosure C1
Network Frequency	50 Hz
Capacitor Technology	3P capacitor
Reactive Power Rating	35 kvar for 400 V AC 50 Hz
Number Of Steps	7 x 5 kvar
Network Rated Voltage	400 V AC 50 Hz 415 V AC 50 Hz
Network Pollution Level	No polluted (0...15 %) at 400 V
[Ui] Rated Insulation Voltage	690 V

Complementary

Device Composition	Contactors Controller equipment regulation Incoming circuit-breaker equipment protection Varplus ² capacitors
Device Wiring	Cables
Internal Voltage Transformer	400/230 V
Capacitor Voltage	415 V AC, 50 Hz
Capacitance Tolerance	- 5 % to 10 %
Rated Short-Duration Power Frequency Withstand Voltage	2.5 kV 50 Hz 1 minute
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours) conforming to IEC 60831
[Imp] Maximum Permanent Current	400 V: 1.3 x I1
Colour Code	RAL 9001
Height	450 mm
Width	500 mm
Depth	275 mm
Net Weight	20 kg

Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Standards	IEC 61921
	EN 60439-1
	IEC 60439-1
Ip Degree Of Protection	IP31
Ambient Air Temperature For Operation	-5...40 °C
Average Ambient Air Temperature For Operation	25 °C (annual)
	35 °C (over 24 hours)

Contractual warranty

Warranty	18 months
----------	-----------