


Product data sheet

Specifications



Thorsman - INKA-LS123 - bend 90° /front cover - 72 mm - white

5507123

Main

Range Of Product	Thorsman
Product Name	Thorsman INKA
Product Or Component Type	Bend 90°
Provided Equipment	Front cover
Colour Tint	White (NCS 0402-B91G)
Quantity Per Set	Set of 1

Complementary

Trunking Material	Aluminium
Trunking Dimension	123 x 72 mm
Material	Aluminium powder coated
Length	200 mm
Height	200 mm
Width	72 mm

Environment

Directives	2014/35/EU - low voltage directive
Standards	EN 50085-1 73/23/EEC 93/68/EEC
Ambient Air Temperature For Operation	-20...60 °C
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.8 cm
Package 1 Width	24.6 cm
Package 1 Length	25.0 cm
Package 1 Weight	702.0 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations