

Product data sheet

Specifications



Residual current protection relay, VigiPacT RH99P, 30mA-30A, 220/240VAC 50/60Hz, front panel mounting

56273

Main

Range	VigiPacT
Device short name	RH99P
Product or component type	Residual current protection relay
Relay application	Protection relay
Mounting support	Front panel
Earth-leakage protection class	Type A
Type of setting	Selector
Residual earth-leakage sensitivity adjustment type	Adjustable 9 settings
Earth-leakage sensitivity	0.03...30 A
Earth-leakage time delay	Instantaneous for 0.03 A Adjustable 9 settings 0...4.5 s for 0.03...30 A
Current sensors compatibility	VigiPacT TOA earth leakage current sensor VigiPacT A earth leakage current sensor VigiPacT L earth leakage current sensor
[I _{th} e] conventional enclosed thermal current	8 A
Minimum load	10 mA at 12 V
[U _s] rated supply voltage	220...240 V AC 50/60 Hz 55...110 %
Power consumption in VA	4 VA
Monitored distribution system	1000 V - AC at 50/60 Hz (maximum) 1000 V - AC at 400 Hz (maximum)
Earthing system	IT TT TN-S
[U _{imp}] rated impulse withstand voltage	8 kV
Reset	Manual reset

Complementary

Test function	Local Remote test
Monitoring	Electronics (continuous) Power supply (continuous) Relay/sensor link (continuous)
Type of measurement	Earth fault current internal measurement, range: 80...100 %

Tamperproof of settings	Protected by sealable cover
Connections - terminals	<p>Auxiliary power supply: terminal block cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12</p> <p>Auxiliary power supply: terminal block cable(s) 0.2...2.5 mm² rigid AWG 24...AWG 12</p> <p>Auxiliary power supply: terminal block cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12</p> <p>Fault: terminal block cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12</p> <p>Fault: terminal block cable(s) 0.2...2.5 mm² rigid AWG 24...AWG 12</p> <p>Fault: terminal block cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12</p> <p>Relay test and fault reset: terminal block cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12</p> <p>Relay test and fault reset: terminal block cable(s) 0.2...2.5 mm² rigid AWG 24...AWG 12</p> <p>Relay test and fault reset: terminal block cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12</p> <p>Sensor: terminal block cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12</p> <p>Sensor: terminal block cable(s) 0.2...2.5 mm² rigid AWG 24...AWG 12</p> <p>Sensor: terminal block cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12</p> <p>Voltage presence: terminal block cable(s) 0.2...2.5 mm² flexible AWG 24...AWG 12</p> <p>Voltage presence: terminal block cable(s) 0.2...2.5 mm² rigid AWG 24...AWG 12</p> <p>Voltage presence: terminal block cable(s) 0.25...2.5 mm² flexible AWG 24...AWG 12</p>
Wire stripping length	<p>Auxiliary power supply: 7 mm</p> <p>Fault: 7 mm</p> <p>Relay test and fault reset: 7 mm</p> <p>Sensor: 7 mm</p> <p>Voltage presence: 7 mm</p>
Tightening torque	<p>Auxiliary power supply: 0.6 N.m</p> <p>Fault: 0.6 N.m</p> <p>Relay test and fault reset: 0.6 N.m</p> <p>Sensor: 0.6 N.m</p> <p>Voltage presence: 0.6 N.m</p>
Width	72 mm
Height	72 mm
Depth	78 mm
Cut-out dimensions	68 x 68 mm
Net weight	0.3 kg
IP degree of protection	<p>IP40 on front face: conforming to EN/IEC 60529</p> <p>IP30 on side parts: conforming to EN/IEC 60529</p> <p>IP20 on connection terminals: conforming to EN/IEC 60529</p>
IK degree of protection	IK07 conforming to EN 50102
Mechanical robustness	<p>Fire resistance conforming to IEC 60695-2-1</p> <p>IK protection 2 joules: IK07 conforming to EN 50102</p> <p>Vibrations 13.2...100 Hz: 0.7 g</p> <p>Vibrations 2...13.2 Hz: +/- 1 mm</p>
Environment	
Overvoltage category	IV
Electrical shock protection class	Class II
Electromagnetic compatibility	<p>Conducted and radiated emissions: , B, conforming to CISPR 11</p> <p>Conducted radio-frequency immunity test: , 3, conforming to IEC 61000-4-6</p> <p>Electrostatic discharge immunity test: , 4, conforming to IEC 61000-4-2</p> <p>High-energy conducted susceptibility: , 4, conforming to IEC 61000-4-5</p> <p>Low-energy conducted susceptibility: , 4, conforming to IEC 61000-4-4</p> <p>Radiated susceptibility: , 3, conforming to IEC 61000-4-3</p>
Relative humidity	95 % at 55 °C
Pollution degree	3 conforming to IEC 60664-1
Ambient air temperature for operation	-35...70 °C
Ambient air temperature for storage	-55...85 °C
Packing Units	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	7.8 cm
Package 1 Width	8.8 cm

Package 1 Length	8.7 cm
Package 1 Weight	308.0 g
Unit Type of Package 2	S03
Number of Units in Package 2	36
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	11.575 kg

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov

Contractual warranty

Warranty	18 months
----------	-----------

Recommended replacement(s)