

# Product data sheet

Specifications



## base unit S10UX for Sepam series 20 - 24...250 V - with basic UMI

59603

⚠ Discontinued on: Dec 31, 2023

⚠ To be end-of-service on: Dec 31, 2030

⚠ Discontinued - Service only

### Main

Range Of Product	Sepam series 20
Device Short Name	S10UX
User Machine Interface Type	Without

### Complementary

Umi Control	Alarm acknowledgement Sepam reset
Display Resolution	128 x 64 pixels
Number Of Key	1
Local Signalling	2 LEDs for Sepam operating status (front face) 9 LEDs for indication of parameters (front face)
Output Type	Annunciation relay: 100...240 V AC 47.5...63 Hz continuous current: 2 A breaking capacity: 1 A cos $\phi$ > 0.3 Annunciation relay: 127 V DC continuous current: 2 A breaking capacity: 0.5 A L/R < 20 ms Annunciation relay: 220 V DC continuous current: 2 A breaking capacity: 0.15 A L/R < 20 ms Annunciation relay: 24 V DC continuous current: 2 A breaking capacity: 2 A L/R < 20 ms Annunciation relay: 48 V DC continuous current: 2 A breaking capacity: 1 A L/R < 20 ms Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 5 A cos $\phi$ > 0.3 making capacity: < 15 A for 200 ms Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 8 A resistive making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.2 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.5 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.7 A resistive making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.1 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.2 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.3 A resistive making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 4 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 6 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 24 V DC continuous current: 8 A breaking capacity: 8 A resistive making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 1 A L/R < 40 ms making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 2 A L/R < 20 ms making capacity: < 15 A for 200 ms Control relay: 48 V DC continuous current: 8 A breaking capacity: 4 A resistive making capacity: < 15 A for 200 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

[Us] Rated Supply Voltage	110/240 V AC 47.5...63 Hz tolerance: - 20...10 % deactivated consumption: < 6 VA maximum consumption: < 15 VA 24/250 V DC tolerance: - 20...10 % deactivated consumption: < 4.5 W maximum consumption: < 8 W
Supply Inrush Current	< 10 A for 10 ms at 24/250 V DC < 15 A at 110/240 V AC
Mounting Mode	Fixed
Mounting Support	Plate
Height	222 mm
Width	176 mm
Depth	129 mm
Net Weight	1.2 kg
Power Frequency Dielectric Withstand	2 kV during 1 min conforming to IEC 60255-5
[Uimp] Rated Impulse Withstand Voltage	5 kV (1.2/50 µs) conforming to IEC 60255-5
Mechanical Robustness	Earthquakes in operation (level: 2) : 1 Gn (vertical axes) conforming to IEC 60255-21-3 Earthquakes in operation (level: 2) : 2 Gn (horizontal axes) conforming to IEC 60255-21-3 Jolts de-energized (level: 2) : 20 Gn/16 ms conforming to IEC 60255-21-2 Shocks de-energized (level: 2) : 30 Gn/11 ms conforming to IEC 60255-21-2 Shocks in operation (level: 2) : 10 Gn/11 ms conforming to IEC 60255-21-2 Vibrations de-energized (level: 2) : 2 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: 2) : 1 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: Fc) : 2 Hz...13.2 Hz, a = +/- 1 mm conforming to IEC 60068-2-6

## Environment

Standards	CSA C22.2 No 14-95 CSA C22.2 No 0.17-00 EN 50263 UL 508 CSA C22.2 No 94-M91
Product Certifications	C22.2 file N° 210625 UL 508 file N° 212533 CE
Fire Resistance	650 °C conforming to IEC 60695-2-11
Ip Degree Of Protection	Other panels: IP20 conforming to IEC 60529 Front panel: IP52 conforming to IEC 60529
Nema Degree Of Protection	Type 12 conforming to NEMA
Immunity To Microbreaks	10 ms

Electromagnetic Compatibility	<p>1 MHz damped oscillating wave: (immunity tests-conducted disturbances), III, 2.5 kV MC, 1 kV MD, conforming to IEC 60255-22-1</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), A or B, 4kV, 2.5 kHz/ 2 kV, 5 kHz, conforming to IEC 60255-22-4</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), IV, 4kV, 2.5 kHz, conforming to IEC 61000-4-4</p> <p>Immunity to magnetic fields at network frequency: (immunity tests-radiated disturbances), IV, 30 A/m (continuous)-300 A/m (13 s), conforming to IEC 61000-4-8</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), III, 10 V/m, 80 MHz...2 GHz, conforming to IEC 61000-4-3</p> <p>Surges: (immunity tests-conducted disturbances), III, 2 kV MC, 1 kV MD, conforming to IEC 61000-4-5</p> <p>1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV MC and MD, conforming to ANSI C37.90.1</p> <p>100 kHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV MC, 1 kV MD, conforming to IEC 61000-4-12</p> <p>Conducted disturbance emission: (emission tests), conforming to IEC 60255-25</p> <p>Conducted disturbance emission: (emission tests), B, conforming to EN 55022</p> <p>Disturbing field emission: (emission tests), conforming to IEC 60255-25</p> <p>Disturbing field emission: (emission tests), A, conforming to EN 55022</p> <p>Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 4 kV contact, conforming to ANSI C37.90.3</p> <p>Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 6 kV contact, conforming to IEC 60255-22-2</p> <p>Fast transient bursts: (immunity tests-conducted disturbances), 4kV, 2.5 kHz, conforming to ANSI C37.90.1</p> <p>Immunity to conducted RF disturbances: (immunity tests-conducted disturbances), 10 V, conforming to IEC 60255-22-6</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), 10 V/m, 80 MHz... 1 GHz, conforming to IEC 60255-22-3</p> <p>Immunity to radiated fields: (immunity tests-radiated disturbances), 35 V/m, 25 MHz... 1 GHz, conforming to ANSI C37.90.2 (1995)</p> <p>Voltage interruptions: (immunity tests-conducted disturbances), 100 %, 10 ms, conforming to IEC 60255-11</p>
-------------------------------	--

Climatic Withstand	<p>Continuous exposure to damp heat (in operation) : Ca: 10 days, 93 % RH, 40 °C (104 °F) conforming to IEC 60068-2-3</p> <p>Continuous exposure to damp heat (in storage) : Ca: 56 days, 93 % RH, 40 °C (104 °F) conforming to IEC 60068-2-3</p> <p>Exposure to cold (in operation) : Ab: - 25 °C (- 13 °F) conforming to IEC 60068-2-1</p> <p>Exposure to cold (in storage) : Ab: - 25 °C (- 13 °F) conforming to IEC 60068-2-1</p> <p>Exposure to dry heat (in operation) : Bb: 70 °C (158 °F) conforming to IEC 60068-2-2</p> <p>Exposure to dry heat (in storage) : Bb: 70 °C (158 °F) conforming to IEC 60068-2-2</p> <p>Influence of corrosion/gaz test 2 (in operation) : C: 21 days, 75 % RH, 25 °C (- 13 °F), 0.5 ppm H2S, 1 ppm SO2 conforming to IEC 60068-2-60</p> <p>Temperature variation with specified variation rate (in operation) : Nb: - 25 °C to 70 °C (- 13 °F to 158 °F) 5 °C/min (41 °F/min) conforming to IEC 60068-2-14</p> <p>Influence of corrosion/gaz test 4 (in operation) : 21 days, 75 % RH, 25 °C, 0.01 ppm H2S, 0.2 ppm SO2, 0.02 ppm NO2, 0.01 ppm Cl2 conforming to IEC 60068-2-60</p> <p>Salt mist (in operation) : Kb/2 conforming to IEC 60068-2-52</p>
--------------------	--

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.6 cm
Package 1 Width	26.6 cm
Package 1 Length	26.7 cm
Package 1 Weight	996.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	3
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	3.701 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

 Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	<a href="#">China RoHS declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>