

Product data sheet

Specifications



core balance current transformer
CSH120 - Sepam series
20,40,60,80 - diam.120 mm

59635

Main

Range Of Product	Sepam series 60 Sepam series 40 Sepam series 20 Sepam series 80 NPP Sepam series 48 Sepam series 80
Device Short Name	CSH120

Complementary

Current Transformer Type	Core balance
Current Transformer Ratio	1/470
Permissible Current	20 kA during 1 s
Mounting Support	Cables Mounting plate
Width	190 mm
Height	164 mm
Depth	44 mm
Diameter	120 mm inner:
Net Weight	0.6 kg

Environment

Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	17.7 cm
Package 1 Length	20.2 cm
Package 1 Weight	691.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	12
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.0 cm
Package 2 Weight	9.415 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Circularity Profile	No need of specific recycling operations