

Product data sheet

Specifications



I/O module MES120NPP - Sepam series 80 NPP - 14 inputs + 6 outputs 24...250 V DC

59715NPP

Main

Module Type	Input/output module
Range Of Product	Sepam series 80 NPP
Device Short Name	MES120NPP

Complementary

Input/Output Type	14 inputs + 6 outputs 24...250 V at DC
Logic Input Number	14 24...250 V 19.2...275 V DC 3 mA 14 V enhanced
Number Of Outputs	1 control relay 5 annunciation relay

Output Type	<p>Annunciation relay: 100...240 V AC 47.5...63 Hz continuous current: 2 A breaking capacity: 0.001 kA cos ϕ > 0.3</p> <p>Annunciation relay: 127 V DC continuous current: 2 A breaking capacity: 0.0005 kA L/R < 20 ms</p> <p>Annunciation relay: 220 V DC continuous current: 2 A breaking capacity: 0.00015 kA L/R < 20 ms</p> <p>Annunciation relay: 24 V DC continuous current: 2 A breaking capacity: 0.002 kA L/R < 20 ms</p> <p>Annunciation relay: 250 V DC continuous current: 2 A breaking capacity: 0.0002 kA L/R < 20 ms</p> <p>Annunciation relay: 48 V DC continuous current: 2 A breaking capacity: 0.001 kA L/R < 20 ms</p> <p>Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 0.005 kA cos ϕ > 0.3 making capacity: < 15 A for 200 ms</p> <p>Control relay: 100...240 V AC 47.5...63 Hz continuous current: 8 A breaking capacity: 0.008 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0002 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0005 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 127 V DC continuous current: 8 A breaking capacity: 0.0007 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0001 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0002 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 220 V DC continuous current: 8 A breaking capacity: 0.0003 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.004 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.006 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 24 V DC continuous current: 8 A breaking capacity: 0.008 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 250 V DC continuous current: 8 A breaking capacity: 0.0002 kA resistive making capacity: < 15 A for 200 ms</p> <p>Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.001 kA L/R < 40 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.002 kA L/R < 20 ms making capacity: < 15 A for 200 ms</p> <p>Control relay: 48 V DC continuous current: 8 A breaking capacity: 0.004 kA resistive making capacity: < 15 A for 200 ms</p>
-------------	---

Height	170 mm
--------	--------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Width	40 mm
Depth	120 mm
Net Weight	0.38 kg
Mechanical Robustness	Earthquakes in operation (level: 2) : 1 Gn (vertical axes) conforming to IEC 60255-21-3 Earthquakes in operation (level: 2) : 2 Gn (horizontal axes) conforming to IEC 60255-21-3 Jolts de-energized (level: 2) : 20 Gn/16 ms conforming to IEC 60255-21-2 Shocks de-energized (level: 2) : 27 Gn/11 ms conforming to IEC 60255-21-2 Shocks in operation (level: 2) : 10 Gn/11 ms conforming to IEC 60255-21-2 Vibrations de-energized (level: 2) : 2 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: 2) : 1 Gn, 10 Hz...150 Hz conforming to IEC 60255-21-1 Vibrations in operation (level: Fc) : 2 Hz...13.2 Hz, a = +/- 1 mm conforming to IEC 60068-2-6
Auxiliary Connection Terminal	Screw-type connectors1 cable(s) 0.2...2.5 mm² Screw-type connectors1 cable(s) 1.5 mm² Screw-type connectors1 cable(s) 2.5 mm² Screw-type connectors2 cable(s) 0.2...1 mm² Screw-type connectors2 cable(s) 1 mm²

Environment

Electromagnetic Compatibility	1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 1 kV DM, conforming to IEC 60255-22-1 1 MHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 2.5 kV DM, conforming to ANSI C37.90.1 100 kHz damped oscillating wave: (immunity tests-conducted disturbances), 2.5 kV CM, 1 kV DM, conforming to IEC 61000-4-12 Conducted disturbance emission: (emission tests), conforming to IEC 60255-25 Conducted disturbance emission: (emission tests), A, conforming to EN 55022 Disturbing field emission: (emission tests), conforming to IEC 60255-25 Disturbing field emission: (emission tests), A, conforming to EN 55022 Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 4 kV contact, conforming to ANSI C37.90.3 Electrostatic discharge: (immunity tests-radiated disturbances), 8 kV air, 6 kV contact, conforming to IEC 60255-22-2 Fast transient bursts: (immunity tests-conducted disturbances), 4kV, 2.5 kHz, conforming to ANSI C37.90.1 Fast transient bursts: (immunity tests-conducted disturbances), A and B, 4kV, 2.5 kHz/2 kV, 5 kHz, conforming to IEC 60255-22-4 Fast transient bursts: (immunity tests-conducted disturbances), IV, 4kV, 2.5 kHz, conforming to IEC 61000-4-4 Immunity to conducted RF disturbances: (immunity tests-conducted disturbances), III, 10 V, conforming to IEC 60255-22-6 Immunity to magnetic fields at network frequency: (immunity tests-radiated disturbances), IV, 30 A/m (continuous)-300 A/m (1-3 s), conforming to IEC 61000-4-8 Immunity to radiated fields: (immunity tests-radiated disturbances), 10 V/m, 80 MHz... 1 GHz, conforming to IEC 60255-22-3 Immunity to radiated fields: (immunity tests-radiated disturbances), 35 V/m, 25 MHz... 1 GHz, conforming to ANSI C37.90.2 Immunity to radiated fields: (immunity tests-radiated disturbances), III, 10 V/m, 80 MHz...2 GHz, conforming to IEC 61000-4-3 Surges: (immunity tests-conducted disturbances), III, 2 kV CM, 1 kV DM, conforming to IEC 61000-4-5 Voltage interruptions: (immunity tests-conducted disturbances), 100 % during 100 ms, conforming to IEC 60255-11
-------------------------------	--

Climatic Withstand	Influence of corrosion/gaz test 2 (in operation) : 21 days, 75 % RH, 25 °C, 0.5 ppm H2S, 1 ppm SO2 conforming to IEC 60068-2-60 Influence of corrosion/gaz test 4 (in operation) : 21 days, 75 % RH, 25 °C, 0.01 ppm H2S, 0.2 ppm SO2, 0.2 ppm NO2, 0.01 ppm Cl2 conforming to IEC 60068-2-60 Continuous exposure to damp heat (in operation) : Cab: 10 days, 93 % RH, 40 °C conforming to IEC 60068-2-78 Continuous exposure to damp heat (in storage) : Cab: 56 days, 93 % RH, 40 °C conforming to IEC 60068-2-78 Continuous exposure to damp heat (in storage) : Db: 6 days, 95 % RH, 55 °C conforming to IEC 60068-2-30 Exposure to cold (in operation) : Ad: - 25 °C conforming to IEC 60068-2-1 Exposure to cold (in storage) : Ab: - 25 °C conforming to IEC 60068-2-1 Exposure to dry heat (in operation) : Bd: 70 °C conforming to IEC 60068-2-2 Exposure to dry heat (in storage) : Bb: 70 °C conforming to IEC 60068-2-2 Salt mist (in operation) : Kb/2: 6 days conforming to IEC 60068-2-52 Temperature variation with specified variation rate (in storage) : Nb: - 25 °C to 70 °C, 5 °C/min conforming to IEC 60068-2-14
--------------------	---

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.5 cm
Package 1 Width	14.5 cm
Package 1 Length	21.5 cm
Package 1 Weight	460.0 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information