


# Product data sheet

Specifications



## Variable speed drive, Altivar Process ATV600, APM, Low Harmonic 600 V, 1000 hp

ATV6B0M10T6

### Main

Range Of Product	Altivar Process ATV600
Product Or Component Type	Variable speed drive
Product Specific Application	Process and utilities
Device Short Name	ATV6B0
Variant	Modular version
Product Destination	Synchronous motors Asynchronous motors
Mounting Mode	Cabinet mount
Kit Composition	1 control unit mechanical mounting kits power connection set of fuses 5.0 power module 200 kW 4 front cover
Emc Filter	Integrated with 300 m conforming to IEC 61800-3 category C3
Ip Degree Of Protection	IP00 (for IP21 or IP54 cabinet integration) conforming to IEC 61800-5-1 IP00 (for IP21 or IP54 cabinet integration) conforming to IEC 60529
Degree Of Protection	UL type 1 conforming to UL 61800-5-1 (cabinet integration) UL type 12 conforming to UL 61800-5-1 (cabinet integration)
Type Of Cooling	Forced convection
Supply Frequency	50...60 Hz - 5...5 %
Network Number Of Phases	3 phases
[Us] Rated Supply Voltage	600 V - 10...15 %
Prospective Line Isc	50 kA
Asynchronous Motor Control Profile	Constant torque standard Variable torque standard Optimized torque mode
Synchronous Motor Control Profile	Permanent magnet motor Synchronous reluctance motor
Speed Drive Output Frequency	0...500 Hz
Nominal Switching Frequency	2.5 kHz
Switching Frequency	2...4.9 kHz adjustable with derating factor
Safety Function	STO (safe torque off) SIL 3
Number Of Preset Speeds	16 preset speeds
Communication Port Protocol	Ethernet Modbus serial Modbus TCP

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

<b>Option Module</b>	Slot A: communication module, Profibus DP V1 Slot A: communication module, PROFINET Slot A: communication module, DeviceNet Slot A: communication module, Modbus TCP/EtherNet/IP Slot A: communication module, CANopen daisy chain RJ45 Slot A: communication module, CANopen SUB-D 9 Slot A: communication module, CANopen screw terminals Slot A/slot B: digital and analog I/O extension module Slot A/slot B: output relay extension module
----------------------	---

## Complementary

<b>Motor Power Hp</b>	1000.0 hp at 600 V normal duty 800.0 hp at 600 V heavy duty
<b>Line Current</b>	785.0 A at 600 V (normal duty) 628.0 A at 600 V (heavy duty)
<b>Apparent Power</b>	815 kVA at 600 V normal duty 652 kVA at 600 V heavy duty
<b>Continuous Output Current</b>	1030.0 A at 2.5 kHz normal duty 830.0 A at 2.5 kHz heavy duty
<b>Maximum Transient Current</b>	1133 A during 60 s (normal duty) 1245 A during 60 s (heavy duty)
<b>Permissible Temporary Current Boost</b>	1.1 x In during 60 s (normal duty) 1.5 x In during 60 s (heavy duty)
<b>Output Voltage</b>	<= power supply voltage
<b>Motor Slip Compensation</b>	Can be suppressed Adjustable Automatic whatever the load Not available in permanent magnet motor law
<b>Acceleration And Deceleration Ramps</b>	S, U or customized Linear adjustable separately from 0.01...9999 s
<b>Braking To Standstill</b>	By DC injection
<b>Protection Type</b>	Thermal protection: motor Safe torque off: motor Motor phase break: motor Thermal protection: drive Safe torque off: drive Overheating: drive Overcurrent between output phases and earth: drive Overload of output voltage: drive Short-circuit protection: drive Motor phase break: drive Overvoltages on the DC bus: drive Line supply overvoltage: drive Line supply undervoltage: drive Line supply phase loss: drive Overspeed: drive Break on the control circuit: drive
<b>Frequency Resolution</b>	Display unit: 0.1 Hz Analog input: 0.012/50 Hz
<b>Electrical Connection</b>	Control: removable screw terminals 0.5...1.5 mm²/AWG 20...AWG 16 Line side: screw terminal Motor: M10 x 2 bars
<b>Physical Interface</b>	2-wire RS 485 for Modbus serial
<b>Transmission Frame</b>	RTU for Modbus serial
<b>Transmission Rate</b>	10/100 Mbit/s for Ethernet IP/Modbus TCP 4.8, 9.6, 19.2, 38.4 kbit/s for Modbus serial
<b>Exchange Mode</b>	Half duplex, full duplex, autonegotiation Ethernet/Modbus TCP
<b>Data Format</b>	8 bits, configurable odd, even or no parity for Modbus serial
<b>Type Of Polarization</b>	No impedance for Modbus serial

Number Of Addresses	1...247 for Modbus serial
Method Of Access	Slave Modbus TCP

## Environment

Maximum Thdi	<5 % full load conforming to IEEE 519
Electromagnetic Compatibility	Electrostatic discharge immunity test level 3 conforming to IEC 61000-4-2 Radiated radio-frequency electromagnetic field immunity test level 3 conforming to IEC 61000-4-3 Electrical fast transient/burst immunity test level 4 conforming to IEC 61000-4-4 1.2/50 $\mu$ s - 8/20 $\mu$ s surge immunity test level 3 conforming to IEC 61000-4-5 Conducted radio-frequency immunity test level 3 conforming to IEC 61000-4-6
Pollution Degree	2 conforming to IEC 61800-5-1
Vibration Resistance	1.5 mm peak to peak (f= 2...13 Hz) conforming to IEC 60068-2-6 0.5 gn (f= 13...200 Hz) conforming to IEC 60068-2-6
Shock Resistance	4 gn for 11 ms conforming to IEC 60068-2-27
Relative Humidity	5...95 % without condensation conforming to IEC 60068-2-3
Ambient Air Temperature For Storage	-40...70 °C
Operating Altitude	< 2000 m with current derating above 1000m
Environmental Characteristic	Chemical pollution resistance class 3C3 conforming to IEC 60721-3-3 Dust pollution resistance class 3S3 conforming to IEC 60721-3-3
Standards	IEC 61800-3 IEC 61800-5-1 IEC 61000-3-12 IEC 60721-3 IEC 61508 IEC 13849-1 UL 61800-5-1
Product Certifications	TÜV UL cUL
Marking	CE