

Product data sheet

Specifications



APC Back-UPS ES 400VA, 230V, 8 BS1363 outlets (4 surge)

BE400-UK

⚠ Discontinued on: Mar 18, 2024

⚠ To be end-of-service on: Mar 31, 2025

⚠ Discontinued - Service only

Overview

Lead Time Usually in Stock

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	240 W
Rated Power In Va	400 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	BS1363A British
Output Connection Type	4 BS 1363 4 BS 1363 surge
Cable Length	1.83 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	User manual Wall-mounting template

Batteries & Runtime

Run Time	View Runtime Graph
Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	16 h
Number Of Battery Replacement Quantity	1
Battery Voltage	12 V
Battery Capacity	6.0 Ah
Battery Charger Power	6 W rated
Battery Power In Vah	102 VAh runtime
Battery Life	2...5 year(s)
Replacement Battery	APCRBC106
Extended Runtime	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Charcoal
Height	8.6 cm
Width	23 cm
Depth	28.5 cm
Net Weight	5.4 kg
Mounting Location	Front
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50/60 Hz
-------------------	----------

Output

Maximum Configurable Power In W	240 W
Output Frequency	47...63 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Ups Type	Standby
Wave Type	Stepped approximation to a sinewave
Maximum Configurable Power In Va	400 VA
Transfer Time	6 ms typical : 10 ms maximum

Conformance

Product Certifications	BSI 1363 CCC CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018
Equipment Protection Policy	Lifetime : 50000 GBP

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...50000 ft
Ambient Air Temperature For Storage	0...40 °C
Storage Relative Humidity	0...95 %

Storage Altitude	0.00...15240.00 m
Acoustic Level	45 dBA

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Control Panel	LED Status display with on line : on battery

Surge Protection and Filtering

Surge Energy Rate	310 J
Noise Suppression	Full time multi-pole noise filtering : 5% IEEE surge let-through : zero clamping response time : meets UL 1449

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13.2 cm
Package 1 Width	30 cm
Package 1 Length	36.6 cm
Package 1 Weight	5.6 kg
Scc14	10731304233401

Contractual warranty

Warranty	2 years repair or replace, 3 years repair or replace for European Union countries
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	End of Life Information