

# Product data sheet

Specifications



## EasyLogic PFC Capacitor, 10.4/12.5 kvar - 480 V - 50/60Hz

BLRCS104A125B48

### Main

Product Or Component Type	Standard duty capacitor
Network Frequency	50/60 Hz
Series Name	EasyLogic PFC Capacitor
Network Harmonic Content	<= 10 %
Electrical Parameters	10.4 kvar 480 V 50 Hz 12.5 kvar 480 V 60 Hz
Maximum Permissible Voltage	1.1 x Un (8 hours over 24 hours)
Continuous Overcurrent Capacity	1.5 x In
Rated Voltage	480 V AC 50/60 Hz

### Complementary

Dielectric Losses	< 0.2 W/kvar
Power Losses	< 0.5 W/kVAr
Capacitance Tolerance	- 5 % to 10 %
Voltage Test	2.15 x Un AC between terminals for 10 s <= 660 V - 3 kV AC between terminal and container for 10 s >= 660 V - 6 kV AC between terminal and container for 10 s
Inrush Current	200 x In
Maximum Switching Operation Per Year	5000
Service Life In Hours	100000 h
Dielectric Material	Metallized polypropylene film with Zn/Al alloy,
Impregnation Material	Non-PCB soft PUR resin Biodegradable
Type Of Installation	Indoor installation
Connections - Terminals	ClampTite terminal
Mounting Mode	Vertical
Diameter	75 mm
Height	233 mm
Net Weight	1.2 kg

### Environment

Standards	IEC 60831-2 IEC 60831-1
Ip Degree Of Protection	IP20

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Operating Altitude	2000 m
Temperature Class	D
Ambient Air Temperature For Operation	-25...55 °C
Relative Humidity	95 %

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	28.5 cm
Package 1 Width	11 cm
Package 1 Length	11.8 cm
Package 1 Weight	1.3 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	2
Package 2 Height	29 cm
Package 2 Width	29 cm
Package 2 Length	39 cm
Package 2 Weight	7.5 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	6
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	9.5 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓   Reach Free Of Svhc

✓   Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	<a href="#">End of Life Information</a>