

Product data sheet

Specifications



Modicon MC80, Controller, 8 DI, 12 DO, 4 AI

BMKC8020301

Main

Range Of Product	Modicon MC80
Product Or Component Type	Processor module
Product Specific Application	Thermo solar - parabolic through

Complementary

Product Compatibility	BMXFTB20... terminal block analog input module BMXFTB28... terminal block discrete I/O module
[Us] Rated Supply Voltage	24 V - 15...20 % DC
Current Consumption	<= 700 mA
Isolation Voltage	1500 V DC
Memory Description	Internal RAM 3840 kB Internal RAM 128 kB data Internal RAM 3590 kB program constants and symbols
Execution Time Per Instruction	0.06 µs Boolean 0.08 µs mixed
Realtime Clock	With
Function Available	Memory retention without battery
Communication Port Protocol	1 non isolated serial link, connector type: RJ45, communication port: RS485/RS232, transmission rate: 0.3...19.2 kbit/s for connecting 247 devices 1 CANopen, connector type: SUB-D 9, transmission rate: 20 kbit/s...1 Mbit/s for connecting 16 devices 2 Ethernet, connector type: RJ45, transmission rate: 10/100 Mbit/s
Integrated Connection Type	USB port: mini B USB connector
Port Ethernet	10BASE-T/100BASE-TX
Bus Length	0...10 m serial link non isolated 0...15 m serial link non isolated 0...1000 m serial link isolated with external isolation tap 0...20 m, transmission rate: 1 Mbit/s, communication port: CANopen 0...2500 m, transmission rate: 20 kbit/s, communication port: CANopen 0...100 m, communication port: Ethernet
Communication Service	Read/write variables for Modbus Diagnostics for Modbus Send/receive character string for character mode Process Data Object (PDO) for CANopen Service Data Object (SDO) for CANopen FDR client for Ethernet SNMP for Ethernet RSTP support for Ethernet
Discrete Input Number	8 positive logic (sink)
Discrete Input Type	Type 3
Discrete Input Current	2.4 mA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Discrete Input Voltage	19...30 V DC
Discrete Output Number	12 positive
Discrete Output Current	2 A per output 10 A per module
Discrete Output Voltage	19...30 V DC
Protection Type	Overload protection for output Short-circuit protection for output
Analogue Input Number	4
Analogue Input Type	Current, input range: - 20...20 mA Voltage, input range: - 10...10 V
Fast Read Cycle Time For Analogue Input	1.3 ms + 1.3 ms x number of channels used
Nominal Read Cycle Time For Analogue Input	6.5 ms for 4 channels
Analogue Input Resolution	16 bits

Environment

Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C
Relative Humidity	0...95 %
Vibration Resistance	3 gn
Marking	CE
Standards	CSA C22.2 No 213 Class I Division 2 Group C CSA C22.2 No 213 Class I Division 2 Group D UL 508 IEC 61131-2 CSA C22.2 No 213 Class I Division 2 Group B CSA C22.2 No 142 CSA C22.2 No 213 Class I Division 2 Group A
Product Certifications	RCM

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.4 cm
Package 1 Width	11.8 cm
Package 1 Length	27.2 cm
Package 1 Weight	1.19 kg
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	7581 kg
Unit Type Of Package 3	P06
Number Of Units In Package 3	48
Package 3 Height	70 cm

Package 3 Width	60 cm
Package 3 Length	80 cm
Package 3 Weight	69148 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)


[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov


Dimensions Drawings

Dimensions




Mounting and Clearance


Mounting on DIN Rails



Mounting on Panels




Clearance



- a : Greater than or equal to 60 mm (2.36 inch)
- b : Greater than or equal to 80 mm (3.15 inch)
- 1 : Installation or casing
- 2 : Wiring duct or tray

Connections and Schema


Discrete I/O Connection



- (1) : Fuse
- (2) : Pre-actuator

Power supply: 24 Vdc
Input fuse: fast blow fuse of 0.5 A
Output fuse: fast blow fuse of 12 A

Analog Input Connection



(1) : Cabling view

(2) : Loopsupply

COM : Common pin for each channel

IVx : Pole input for channel x

ICx: Current reading resistor + input

FG: Functional ground