

Product data sheet

Specifications



Stago - KG281 tray side perforation 60x120mm L=6.4m 1mm pre- galvanized RAL9016

CSU0860284916

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Main

Range Of Product	Stago
Product Or Component Type	Cable tray
Cable Support Type	Perforated
Mounting Location	Partly outdoor environment with low exposure to corrosion ware-houses and parking garages

Complementary

Product Destination	KG281 cable tray
Fixing Mode	Screwless
Material With Surface Treatment	Steel pre-galvanized, RAL 9016
Corrosion Class	C2
Thickness	1 mm
Perforation Location	Side perforation
Nominal Cross Section	7200 mm²
Height	60 mm
Width	120 mm
Length	6400 mm
Net Weight	2.095 kg / 100 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6 cm
Package 1 Width	12 cm
Package 1 Length	100 cm
Package 1 Weight	2.055 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations