

Product data sheet

Specifications



Stago - t-piece H16 - 100x500 mm - steel - hot-dip galvanized

CSU737049

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

Important message: This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link www.wibe-group.com for further details.

Main

Range Of Product	Stago
Product Or Component Type	T-piece
Cable Support Type	High side
Mounting Location	Area with high level of environmental corrosion, humidity and airborne pollution industrial and coastal areas, chemical plants

Complementary

Operating Angle	90 °
Direction Change Type	Horizontal
Product Destination	Cable ladder LB4000 H= 100 mm W= 500 mm Cable ladder WHS H= 100 mm W= 500 mm
Type Of Rung	C-profile
Fixation Rung	Welded
Mounting Mode	Push-in
Fixing Mode	By nut
Material With Surface Treatment	Steel hot-dip galvanized
Corrosion Class	C3/C4
Perforation Location	Side perforation
Height	100 mm
Width	500 mm
Net Weight	8.685 kg / set of 100

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations