

# Product data sheet

Specifications



Fuse carrier, TeSys DF, 3P+N, 25A, 400VAC, fuse size 8.5x31.5mm, blown fuse indicator

DF83NV

⚠ Discontinued on: Dec 29, 2023

⚠ Discontinued

## Main

Range	TeSys
Product Name	TeSys DF
Product Or Component Type	Fuse carrier
Device Short Name	DF8
Device Composition	tubular link for locked in Neutral pole
Product Compatibility	DF2BA fuse cartridge DF2BN fuse cartridge
Poles Description	3P + N
Fuse Size	8.3 x 31.5 mm
Fuse Type	, aM , gG
Control Type	Toggle padlockable
Local Signalling	Blown fuse indication
Utilisation Category	AC-20B conforming to IEC 60947-3
[Ue] Rated Operational Voltage	400 V AC
[Ie] Rated Operational Current	25 A at 400 V AC
[Ith] Conventional Free Air Thermal Current	25 A 20 °C
[Ui] Rated Insulation Voltage	500 V AC
[Uimp] Rated Impulse Withstand Voltage	6 kV
Overvoltage Category	III
Short-Circuit Withstand	20 kA 400 V conforming to IEC 60947-3
Power Dissipation In W	2.5 W maximum power dissipation by fuse

## Complementary

Standards	EN/IEC 60947-3 EN/IEC 60269-2
Product Certifications	IEC EAC DNV-GL
Mounting Support	35 mm symmetrical DIN rail
Mounting Position	Vertical (tolerance: +/- 23°)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Connections - Terminals	Screw clamp terminals 1 cable(s) 1...16 mm²rigid Screw clamp terminals 2 cable(s) 1...6 mm²rigid Screw clamp terminals 1 cable(s) 1...16 mm²flexible with or without Screw clamp terminals 2 cable(s) 1...6 mm²flexible with or without
Tightening Torque	2.2 N.m - with screwdriver PZ2 2.2 N.m - with screwdriver flat Ø 5.5 mm
Height	79.5 mm
Width	70 mm
Depth	61 mm
Net Weight	0.171 kg
Quantity Per Set	Set of 3

## Environment

Ambient Air Temperature For Storage	-40...70 °C
Ambient Air Temperature For Operation	-40...70 °C with derating above 20°C
Operating Altitude	0...2000 m without derating
Ip Degree Of Protection	IP20
Pollution Degree	3
Fire Resistance	960 °C conforming to IEC 60695-2-1
Compatibility Code	DF8

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.2 cm
Package 1 Width	7.2 cm
Package 1 Length	8 cm
Package 1 Weight	183 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	3
Package 2 Height	7.1 cm
Package 2 Width	8.7 cm
Package 2 Length	22.3 cm
Package 2 Weight	584 g
Unit Type Of Package 3	S03
Number Of Units In Package 3	12
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	2.823 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability





**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Reach Free Of Svhc	
	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Reach Regulation		<a href="#">REACH Declaration</a>
Eu Rohs Directive		Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation		<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee		The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65		WARNING: Cancer - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>