

Product data sheet

Specifications



Cable ends, Linergy TR cable ends, single conductor, for un-insulated cable, 0.75mm², medium size, 10 sets of 100

DZ5CE007N

Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	DIN 46228-1
Type Of Packing	String of bags
Quantity Per Set	10 sets of 100
Cable Cross Section	0.75 mm ²

Complementary

Cable End Type	Single conductor
Additional Information	Non-insulated
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	1
Awg Gauge	AWG 20
Bezel Size	Ø 3.3 mm
Tube Diameter	1.5 mm
Length	8 mm
Tube Length	8 mm
Net Weight	0.1 kg

Environment

Ambient Air Temperature For Operation	-20...105 °C
---------------------------------------	--------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm
Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	1000
Package 2 Height	2.000 cm
Package 2 Width	6.500 cm
Package 2 Length	18.000 cm
Package 2 Weight	66.000 g
Unit Type Of Package 3	S01
Number Of Units In Package 3	7000
Package 3 Height	15.000 cm
Package 3 Width	15.000 cm
Package 3 Length	40.000 cm
Package 3 Weight	651.000 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations