


Product data sheet

Specifications



10A 2 GANG 1 WAY SWITCH W. FLUORES, GREY SILVER

E3032H1_FGGS_G19

 **Discontinued on:** Dec 17, 2020

 **Discontinued**

Main

| | |
|---------------------------|---|
| Range | Neo |
| Product Or Component Type | Control switch |
| Wiring Device Mounting | Flush Surface |
| Switch Function | 1-way |
| Switch Application | Switch |
| Load Type | Incandescent lamp Resistive Fluorescent lamp Inductive |
| Bulb Type | Fluorescent (green) |
| Colour Tint | Grey silver |

Complementary

| | |
|------------------------------|--|
| Rated Current | 10 A at 250 V AC 50/60 Hz |
| Number Of Gangs | 2 gangs horizontal |
| Material | Brass: metal parts Polycarbonate: plastic part Steel: metal parts |
| Clamping Connection Capacity | 3 x 2.5 mm ² for solid cable(s) 3 x 2.5 mm ² for stranded cable(s) 4 x 1.5 mm ² for solid cable(s) 4 x 1.5 mm ² for stranded cable(s) |
| Connections - Terminals | Pillar terminals |
| Width | 87 mm |
| Height | 87 mm |
| Embedding Depth | 23.5 mm |
| Depth | 36 mm |

Environment

| | |
|---------------------------------------|---|
| Ambient Air Temperature For Operation | 0...40 °C |
| Relative Humidity | 0...95 % |
| Environmental Characteristic | Indoor use |
| Standards | EN 60669-1 IEC 60669-1 GB 16915.1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|-----------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile | End of Life Information |