

# Product data sheet

Specifications



## 10A 3 GANG 1 WAY SWITCH W. FLUORES, GREY SILVER

E3033V1\_FGGS\_G19

 **Discontinued on:** Dec 17, 2020

 **Discontinued**

### Main

|                           |                                                                 |
|---------------------------|-----------------------------------------------------------------|
| Range                     | Neo                                                             |
| Product Or Component Type | Control switch                                                  |
| Wiring Device Mounting    | Flush<br>Surface                                                |
| Switch Function           | 1-way                                                           |
| Switch Application        | Switch                                                          |
| Load Type                 | Inductive<br>Resistive<br>Fluorescent lamp<br>Incandescent lamp |
| Bulb Type                 | Fluorescent (green)                                             |
| Colour Tint               | Grey silver                                                     |

### Complementary

|                              |                                                                                                                                                                                            |
|------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Rated Current                | 10 AX at 250 V AC 50/60 Hz                                                                                                                                                                 |
| Number Of Gangs              | 3 gangs vertical                                                                                                                                                                           |
| Material                     | Brass: metal parts<br>Polycarbonate: plastic part<br>Steel: metal parts                                                                                                                    |
| Clamping Connection Capacity | 3 x 2.5 mm <sup>2</sup> for solid cable(s)<br>3 x 2.5 mm <sup>2</sup> for stranded cable(s)<br>4 x 1.5 mm <sup>2</sup> for solid cable(s)<br>4 x 1.5 mm <sup>2</sup> for stranded cable(s) |
| Connections - Terminals      | Pillar terminals                                                                                                                                                                           |
| Width                        | 87 mm                                                                                                                                                                                      |
| Height                       | 87 mm                                                                                                                                                                                      |
| Embedding Depth              | 23.5 mm                                                                                                                                                                                    |
| Depth                        | 36 mm                                                                                                                                                                                      |

### Environment

|                                       |                                         |
|---------------------------------------|-----------------------------------------|
| Ambient Air Temperature For Operation | 0...40 °C                               |
| Relative Humidity                     | 0...95 %                                |
| Environmental Characteristic          | Indoor use                              |
| Standards                             | EN 60669-1<br>IEC 60669-1<br>GB 16915.1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

|                       |                                                                                                             |
|-----------------------|-------------------------------------------------------------------------------------------------------------|
| Reach Regulation      | <a href="#">REACH Declaration</a>                                                                           |
| Eu Rohs Directive     | Compliant<br><a href="#">EU RoHS Declaration</a>                                                            |
| China Rohs Regulation | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Circularity Profile   | <a href="#">End of Life Information</a>                                                                     |