

Product data sheet

Specifications



Miniature circuit breaker (MCB),
Acti9 iC40, 1P+N, 32A, B curve,
4500A (IEC/EN 60898-1), 6kA (IEC/
EN 60947-2)

A9P42632

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	Acti9
Product Name	Acti9 iC40
Product Or Component Type	Miniature circuit-breaker
Device Short Name	iC40
Device Application	Distribution
Poles Description	1P + N
Number Of Protected Poles	1
Neutral Position	Left
[In] Rated Current	32 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	B
Breaking Capacity	6 kA Icu at 230 V AC 50/60 Hz conforming to EN/IEC 60947-2 4500 A Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1
Suitability For Isolation	Yes conforming to EN/IEC 60947-2
Quality Labels	KEMA IMQ

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	230 V AC 50/60 Hz
Magnetic Tripping Limit	3...5 x In conforming to EN/IEC 60898-1 4 x In +/- 20 % conforming to EN/IEC 60947-2
[Ics] Rated Service Breaking Capacity	4500 A 100 % x Icn at 230 V AC 50/60 Hz conforming to EN/IEC 60898-1 4.5 kA 75 % x Icu at 230 V AC 50/60 Hz conforming to EN/IEC 60947-2
Limitation Class	3 conforming to EN/IEC 60898-1
[Ui] Rated Insulation Voltage	400 V AC 50/60 Hz conforming to EN/IEC 60947-2
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to EN/IEC 60947-2
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	ON/OFF indication Trip indicator

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	2
Height	85 mm
Width	18 mm
Depth	74 mm
Net Weight	120 g
Colour	White
Mechanical Durability	20000 cycles
Electrical Durability	10000 cycles
Locking Options Description	Padlocking device
Connections - Terminals	Tunnel type terminals top or bottom 1...10 mm² flexible Tunnel type terminals top or bottom 1...16 mm² rigid
Wire Stripping Length	14 mm for top or bottom connection
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Separate block

Environment

Standards	EN/IEC 60898-1 EN/IEC 60947-2
Product Certifications	CE BV RINA DNV
Ip Degree Of Protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution Degree	3 conforming to EN/IEC 60947-2
Relative Humidity	95 % at 55 °C
Operating Altitude	2000 m
Ambient Air Temperature For Operation	-25...70 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	1.8 cm
Package 1 Length	9.4 cm
Package 1 Weight	122.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	12
Package 2 Height	8.1 cm
Package 2 Width	9.9 cm
Package 2 Length	22.4 cm

Package 2 Weight	1.527 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	132
Package 3 Height	30.0 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	17.255 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Halogen Free Product

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations