

Product data sheet

Specifications



Easy UPS 3M Classic Battery Cabinet with batteries, IEC, 1000mm wide - Config B

E3MCBC10B

Overview

Presentation	Battery cabinet that includes batteries and battery breaker.
Lead Time	Usually Ships within 6 Weeks

Main

Product Or Component Type	Battery cabinet
Battery Type	VRLA
Provided Equipment	Installation guide

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Enclosed battery cabinet

Physical

Height	189.5 cm
Width	100.2 cm
Depth	84.5 cm
Net Weight	1277 kg
Mounting Mode	Not rack-mountable

Environmental

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-15...40 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	198 cm
Package 1 Width	97 cm
Package 1 Length	113 cm
Package 1 Weight	1297 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information