

# Product data sheet

Specifications



## 450W 240V 1 Gang Fan Controller with Switch

E8232V450F\_MB\_G1

### Main

Product or component type	Fan controller
Number of gangs	1 gang
Rated operational voltage	250 V AC 50 Hz
Operational power in W	450 W

### Complementary

Wiring device mounting	Surface Flush
Material	Polycarbonate: plastic part
Width	87 mm
Height	87 mm
Depth	55 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Operating altitude	2000 m
Standards	IEC 60669

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.35 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	104.53 g
Unit Type of Package 2	CAR
Number of Units in Package 2	60
Package 2 Height	21 cm
Package 2 Width	32.5 cm

Package 2 Length	50 cm
Package 2 Weight	6271.8 g
Unit Type of Package 3	PAL
Number of Units in Package 3	1200
Package 3 Height	84 cm
Package 3 Width	82.5 cm
Package 3 Length	100 cm
Package 3 Weight	142436 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
RoHS exemption information	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Recommended replacement(s)