

Product data sheet

Specifications



Conventional beacon, CWST-RW-W5-E010, wall and ceiling, IP65

FFS06711061

Main

Range Of Product	Esmi conventional components
Product Or Component Type	Visual alarm device

Complementary

Colour Tint	Body: red Lens: clear
Device Composition	body in PC/ABS lens in PC (polycarbonate)
[Ue] Rated Operational Voltage	12...29 V DC
Current Consumption	26 mA at 29 V DC
Local Signalling	LED white flashing at 0.5 Hz: alarm
Coverage Class	W-2.4-9.0 C-3-9.5 C-6-9.5 C-9-9.5
Cable Cross Section	0.5...2.5 mm²
Diameter	100 mm
Height	97 mm
Net Weight	171 g

Environment

Standards	EN 54-23
Product Certifications	CPR LPCB
Ip Degree Of Protection	IP65
Relative Humidity	0...96 % non-condensing
Ambient Air Temperature For Operation	-25...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	10.0 cm
Package 1 Width	15.0 cm
Package 1 Length	15.0 cm
Package 1 Weight	204.0 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information