

Product data sheet

Specifications



MGE Galaxy 3500 Maintenance Bypass Cabinet 10-15kVA 208V Floormount

G35TSBP10K15F

! Discontinued

! Discontinued on: Jul 5, 2021

! End-of-service on: Feb 21, 2024

Overview

Lead Time Usually Ships within 2 Weeks

Main

Main Input Voltage 208 V 3 phases

Main Output Voltage 208 V 3 phases

Rated Power In Va 30000 VA

Provided Equipment Installation guide

Physical

Height 148.7 cm

Width 35.1 cm

Depth 83.7 cm

Net Weight 127 kg

Mounting Support Floor

Mounting Preference No preference

Mounting Mode Not rack-mountable

Input

Network Frequency 60 Hz

Conformance

Standards CSA C22.2 No 107.1
UL 1778

Product Certifications CSA

Environmental

Ambient Air Temperature For Operation 0...40 °C

Relative Humidity 0...95 %

Operating Altitude 0...10000 ft

Ambient Air Temperature For Storage 0...45 °C

Storage Relative Humidity 0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Storage Altitude	0.00...9144.00 m
------------------	------------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	166.37 cm
Package 1 Width	110.49 cm
Package 1 Length	72.39 cm
Package 1 Weight	156 kg

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
-------------------	--
