

Product data sheet

Specifications

Actassi Indoor Fiber Cable Tight Buffered BISM 9/125µm 12-Core LSZH



ACTND12SM9BLS

Main

Range	Actassi
Product	Fibre optic cable single mode
Device Application	Communication
Cable Packaging	Reel

Complementary

Maximum Attenuation	0.4 dB / 1 km at 1550 nm 0.5 dB / 1 km at 1310 nm
Fibre Performance	OS2 9/125 µm
Optic Fibre Type	Tight buffered diameter: 900 µm
Number Of Optic Fibre	12
Bending Radius	10 x overall diameter long term 20 x overall diameter short term
Pulling Force	660 N installed 220 N operation
Crush Resistance	10000 N/m
Colour	Sheath: yellow
Type Of Installation	Indoor
Diameter	6.2 mm cable +/- 0.2 mm
Cable Weight	40.3 kg / 1 km
Targeted Region	Asia Pacific.

Environment

Ambient Air Temperature For Operation	-20...60 °C
Ambient Air Temperature For Storage	-20...60 °C
Flame Retardance	LSZH
Environmental Characteristic	Strength: aramid yarn Flame retardant:
Standard	conforming to IEC 60332-3C conforming to IEC 754-3 conforming to NES 713 conforming to IEC 1034

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1
Package 1 Height	0.001 cm
Package 1 Width	0.001 cm
Package 1 Length	0.001 cm
Package 1 Weight	0.08 g

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations