

Product data sheet

Specifications



Actassi - patch cord - category 6 - 1-end secure - ID-3 F² - UTP - 2 m - white

ACTPCC6UBCM1E20WE

⚠ Discontinued on: Dec 15, 2021

⚠ Discontinued

Main

Range	Actassi
Device Short Name	ID-3
Product	Patch cord
Colour	White
Cable Shielding Type	F ² /UTP
Provided Component	keys coloured clips

Complementary

Type Of Cable	4 pair cables
[In] Rated Current	1.5 A
Insulation Resistance	>= 500 MOhm
Length (Customizable Value In Configurator)	0...2 m
Communication Network Category	6
Contacts Material	Copper alloy with 50μ gold-plated
Contact Resistance	10000 μOhm
Awg Gauge	AWG 24
Attenuation	Guaranteed: 1.9 dB @ 1 MHz per 105 m cable Guaranteed: 11 dB @ 31.25 MHz per 105 m cable Guaranteed: 15.7 dB @ 62.5 MHz per 105 m cable Guaranteed: 20.1 dB @ 100 MHz per 105 m cable Guaranteed: 28.7 dB @ 200 MHz per 105 m cable Guaranteed: 3.9 dB @ 4 MHz per 105 m cable Guaranteed: 32.2 dB @ 250 MHz per 105 m cable Guaranteed: 6.2 dB @ 10 MHz per 105 m cable Guaranteed: 7.9 dB @ 16 MHz per 105 m cable Guaranteed: 8.8 dB @ 20 MHz per 105 m cable
Power Sum Far End Crosstalk [Psfext]	58.9 dB at 250 MHz 60.6 dB at 200 MHz 64.9 dB at 100 MHz 65 dB at 62.5 MHz 67.9 dB at 31.25 MHz 69.5 dB at 20 MHz 76.3 dB at 16 MHz 83.1 dB at 10 MHz 83.4 dB at 4 MHz 91.2 dB at 1 MHz
Minimum Number Of Matings	1000 cycles
Targeted Region	Asia Pacific.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Temperature Resistance	75 °C
Product Certifications	UL
Standards	TIA/EIA-568-B ISO/IEC 11801

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	30.2 cm
Package 1 Width	2 cm
Package 1 Length	21 cm
Package 1 Weight	115 g

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations