

Product data sheet

Specifications



MGE Galaxy 5500 20KVA 400V Single UPS BACK UP INCL T1, Start-up 5x8

G55TUPSU20HB15S

! Discontinued

! Discontinued on: Jul 5, 2021

! End-of-service on: Oct 18, 2023

Overview

Presentation	A versatile 3-phase UPS for facility, industrial and data center applications. Configurable system with a comprehensive range of accessories to meet your application demands.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated Power In W	18000 W
Rated Power In Va	20000 VA
Output Connector Type	Hard wire 4-wire (3P + E) 1
Battery Type	VRLA
Provided Equipment	Installation guide User manual

Batteries & Runtime

Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	10 h
Additional Information	Estimated runtimes only. Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Battery Voltage	432 V
Battery Charger Power	984 W rated
Battery Power In Vah	9850 VAh runtime
Battery Life	8...10 year(s)
Battery Graph Comments	Estimated runtimes based on battery vendor data, at typical environmental conditions, with no electrical input and balanced PF = 0.8 output.
Extended Runtime	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Bypass Voltage Tolerance	+/- 10 % settable from +/- 4/6/8 and 10 %
Max Bypass Input Current	29 A
Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Height	190 cm
Width	111 cm
Depth	85 cm
Net Weight	738 kg
Mounting Preference	No preference
Usb Compatible	No

Input

Network Frequency	45...65 Hz
Number Of Input Connectors	1 hard wire 4-wire (3P + E) 1 hard wire 4-wire (3P + N)
Input Voltage Limits	323...437 V 380 V 340...460 V 400 V 353...477 V 415 V
Maximum Input Current	42 A
Switching Current Capacity	125 A
Max Short Time Withstand Current	20 kA
Input Harmonic Distortion	Less than 5 % for full load
Input Protection Type	GL fuse
Load Power Factor	0.9
Input Power Factor At Full Load	1

Output

Maximum Configurable Power In W	18000 W
Harmonic Distortion	Less than 2 %
Output Frequency	50/60 Hz +/- 3 Hz user adjustable +/- 0.1 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	2.5 : 1
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 5% at 100% load step
Output Harmonic Distortion	< 1% linear load and < 2.5% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Required Output Current Protection	29 A
Bypass Type	Built-in maintenance bypass Built-in static bypass Optional external bypass

Maximum Output Current	190 A
Maximum Configurable Power In Va	20000 VA

Conformance

Product Certifications	CE TÜV VDE
Standards	IEC 62040-1-2 EN/IEC 62040-2 EN/IEC 62040-3 ISO 9001

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-20...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...12192.00 m
Acoustic Level	55.5 dBA
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	2
Preinstalled Device	Network management card 2 with environmental monitoring, out of band access and Modbus
Control Panel	Multifunction LCD status and control console
Emergency Power Off	Yes

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203 cm
Package 1 Width	96 cm
Package 1 Length	113 cm
Package 1 Weight	978 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up, 1 year (parts only)
----------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive

Under investigation
