

Product data sheet

Specifications



MGE Galaxy 5000 40 kVA

G5TUPS40

⚠ Discontinued on: Jul 5, 2021

⚠ End-of-service on: Oct 18, 2023

⚠ Discontinued

Overview

Presentation	A versatile 3-phase UPS for facility, industrial and data center applications. Configurable system with a comprehensive range of accessories to meet your application demands.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases 480 V 3 phases 600 V 3 phases
Other Input Voltage	380 V 400 V 415 V 480 V 600 V
Main Output Voltage	400 V 3 phases 480 V 3 phases 600 V 3 phases
Other Output Voltage	208 V 220 V 380 V 400 V 415 V 600 V
Rated Power In W	36000 W
Rated Power In Va	40000 VA
Output Connector Type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1
Battery Type	External battery system
Provided Equipment	Installation guide User manual

Batteries & Runtime

Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Additional Information	Configurable for 380 : 400 or 415 V 3 Phase nominal output voltage
Battery Power In Vah	0 VAh runtime
Extended Runtime	0

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No

Physical

Colour	Charcoal
Height	190 cm
Width	71.2 cm
Depth	84.8 cm
Net Weight	400 kg
Mounting Preference	No preference
Usb Compatible	No

Input

Network Frequency	45...65 Hz
Number Of Input Connectors	1 hard wire 4-wire (3P + E)
Input Voltage Limits	340...460 V 400 V 408...538 V
Maximum Input Current	77 A
Switching Current Capacity	125 A
Max Short Time Withstand Current	20 kA
Input Harmonic Distortion	Less than 3 % for full load
Input Protection Type	3-pole circuit breaker
Load Power Factor	0.9
Input Power Factor At Full Load	1

Output

Maximum Configurable Power In W	36000 W
Harmonic Distortion	Less than 2 %
Output Frequency	50 Hz programmable +/- 0.5 / 1 / 2 / 4 / 6 / 8 % sync to mains 60 Hz sync to mains 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	3 : 1
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 2 % at 100% load step
Output Harmonic Distortion	< 1% linear load and < 2.5% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Neutral Output Current	87 A
Bypass Type	Internal bypass (automatic and manual) Optional external bypass
Maximum Output Current	190 A

Maximum Configurable Power In Va	40000 VA
----------------------------------	----------

Conformance

Product Certifications	CE TÜV VDE
Standards	EN/IEC 62040-1-1 EN/IEC 62040-3 IEC 60950 IEC 61000-3-2 IEC 61000-3-3 EN 61000-4-5 IEC 62040-1-2 IEC 62040-2 ISO 9001

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-20...45 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...3048.00 m
Acoustic Level	66 dBA
Heat Dissipation	8974 Btu/h

Communications & Management

Free Slots	3
Control Panel	Multifunction LCD status and control console
Emergency Power Off	Optional

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	203 cm
Package 1 Width	96 cm
Package 1 Length	98 cm
Package 1 Weight	420 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up, 1 year (parts only)
----------	--

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov