

# Product data sheet

Specifications



Cable end, Linergy TR cable ends, twin conductor, blue, 0.75mm<sup>2</sup>, for insulated cable, medium size, 5 sets of 50

AZ5DE007

## Main

Range Of Product	Linergy
Product Or Component Type	Cable end
Cable End Size	Medium
Standards	NF C 63-023
Type Of Packing	Dispenser pack
Quantity Per Set	5 sets of 100
Cable Cross Section	0.75 mm <sup>2</sup>

## Complementary

Cable End Type	Twin conductor
Additional Information	Without marker tag holder
Colour	Blue
Bezel Material	Halogen-free plastic
Tube Material	Copper conforming to ISO 1337
Number Of Cables	2
Awg Gauge	AWG 20
Bezel Size	Ø 2.8 x 5 mm
Tube Diameter	2 mm
Length	15 mm
Tube Length	8 mm
Net Weight	0.13 kg

## Environment

Product Certifications	cCSAus
Ambient Air Temperature For Operation	-20...105 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.400 cm
Package 1 Width	0.400 cm
Package 1 Length	1.400 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	0.100 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	500
Package 2 Height	13.000 cm
Package 2 Width	7.000 cm
Package 2 Length	12.500 cm
Package 2 Weight	134.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	20000
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	6.214 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

✓ Pvc Free

✓ Halogen Free Plastic Parts Product

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations