

Product data sheet

Specifications



redundant power supply module, Modicon X80, 24 to 48V DC

BMXCPS4022

Main

Range Of Product	Modicon X80
Product Or Component Type	Power supply module
Backplane Compatibility	All backplane
Advanced Diagnostics Available Via Network	Redundancy information Redundancy test Temperature sensing Remaining lifetime Uptime duration
Primary Voltage	24...48 V
Supply Circuit Type	DC
Secondary Power	18 W 3.3 V DC at 0...60 °C I/O module logic power supply 40 W 24 V DC at 0...60 °C I/O module power supply and processor if 3.3 V not loaded

Complementary

Primary Voltage Limit	18...62.4 V
Input Current	1.9 A 24 V 1 A 48 V
Inrush Current	60 A 48 V 60 A 24 V
I²T On Activation	0.4 A².s 24 V 1.9 A².s 48 V
It On Activation	0.05 A.s 24 V 0.08 A.s 48 V
Mtbf Reliability	752000 H
Protection Type	Internal fuse not accessible for primary circuit Overload protection for secondary circuit Overvoltage protection for secondary circuit Short-circuit protection for secondary circuit
Current At Secondary Voltage	5.5 A 3.3 V DC I/O module logic power supply 1.67 A 24 V DC I/O module power supply and processor
Maximum Power Dissipation In W	8.5 W
Status Led	1 LED (green) presence of voltages (OK) 1 LED (green) redundancy OK 1 LED (green) power supply status
Control Type	RESET push-button cold restart
Electrical Connection	1 connector 2 pin(s)alarm relay 1 connector 5 pin(s)line supply, protective earth
Maximum Cable Distance Between Devices	10 m 15 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Insulation Resistance	>= 100 MOhm primary/ground >= 100 MOhm primary/secondary
Net Weight	0.81 kg

Environment

Immunity To Microbreaks	1 ms
Dielectric Strength	1500 V primary/ground 1500 V primary/secondary
Ip Degree Of Protection	IP20
Directives	2014/35/EU - low voltage directive 2014/30/EU - electromagnetic compatibility
Environmental Characteristic	3C3 conforming to IEC 60721-3-3 3C4 conforming to IEC 60721-3-3
Ambient Air Temperature For Storage	-40...85 °C
Ambient Air Temperature For Operation	0...60 °C
Relative Humidity	10...95 % without condensation

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	18 cm
Package 1 Width	25 cm
Package 1 Length	9 cm
Package 1 Weight	660 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	6
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4.4 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	48
Package 3 Height	60 cm
Package 3 Width	80 cm
Package 3 Length	70 cm
Package 3 Weight	43.2 kg

Sustainability



Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Well-being performance

 Mercury Free	
 Rohs Exemption Information	Yes
Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)
China Rohs Regulation	China RoHS declaration
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov