

Product data sheet

Specifications



Galaxy VM Battery Breaker Box 630A EL

GVMBBB630EL

Overview

Presentation	Wall mounted battery breaker box for use with open battery rack configurations.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	400 V 3 phases
Battery Type	External battery system
Provided Equipment	Installation guide

Batteries & Runtime

Number Of Battery Free Slots	0
Number Of Battery Filled Slots	0
Device Mounting	Open frame battery stands
Battery Power In Vah	0 VAh

Physical

Height	81 cm
Width	51.1 cm
Depth	29.1 cm
Net Weight	40 kg
Mounting Mode	Not rack-mountable

Conformance

Standards	EN/IEC 62040-2 EN/IEC 62040-3 IBC 2012 and CBC2013 to Sds=2.02g UL 1778 VFI-SS-111
Product Certifications	C-Tick CE RCM

Environmental

Ambient Air Temperature For Operation	0...40 °C
Operating Altitude	0...3333 ft
Relative Humidity	0...95 %

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-25...65 °C
Storage Altitude	0.00...14999.82 m
Storage Relative Humidity	0...95 %

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	82 cm
Package 1 Width	30 cm
Package 1 Length	52 cm
Package 1 Weight	45 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive Pro-active compliance (Product out of EU RoHS legal scope)

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)