

# Product data sheet

Specifications



## Galaxy VM Battery Breaker Kit 630A EL

GVMBBK630EL

### Overview

|              |  |
|--------------|--|
| Presentation | Battery circuit breaker kit protects the DC cables from batteries to the UPS. For use with Galaxy VM empty battery cabinets. |
| Lead Time    | Usually Ships within 2 Weeks   |

### Main

|                    |                         |
|--------------------|-------------------------|
| Main Input Voltage | 400 V 3 phases          |
| Battery Type       | External battery system |
| Provided Equipment | Installation guide      |

### Batteries & Runtime

|                                |                           |
|--------------------------------|---------------------------|
| Number Of Battery Free Slots   | 0                         |
| Number Of Battery Filled Slots | 0                         |
| Device Mounting                | Open frame battery stands |
| Battery Power In Vah           | 0 VAh                     |

### Physical

|               |                    |
|---------------|--------------------|
| Colour        | White              |
| Height        | 26.2 cm            |
| Width         | 37.7 cm            |
| Depth         | 76.6 cm            |
| Net Weight    | 11.88 kg           |
| Mounting Mode | Not rack-mountable |

### Conformance

|                        |  |
|------------------------|--|
| Standards              | EN/IEC 62040-1<br>EN/IEC 62040-2<br>EN/IEC 62040-3<br>IBC 2012 and CBC2013 to Sds=2.02g<br>UL 1778<br>VFI-SS-111 |
| Product Certifications | C-Tick<br>CE<br>RCM  |

### Environmental

|                                       |           |
|---------------------------------------|-----------|
| Ambient Air Temperature For Operation | 0...40 °C |
|---------------------------------------|-----------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                     |                   |
|-------------------------------------|-------------------|
| Operating Altitude                  | 0...3333 ft       |
| Relative Humidity                   | 0...95 %          |
| Ambient Air Temperature For Storage | -25...40 °C       |
| Storage Altitude                    | 0.00...14999.82 m |
| Storage Relative Humidity           | 0...95 %          |

## Packing Units

|                              |         |
|------------------------------|---------|
| Unit Type Of Package 1       | PCE     |
| Number Of Units In Package 1 | 1       |
| Package 1 Height             | 27.9 cm |
| Package 1 Width              | 81.3 cm |
| Package 1 Length             | 40.6 cm |
| Package 1 Weight             | 11.9 kg |

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient   Take-back   Transparency

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Rohs Exemption Information   [Yes](#)

Eu Rohs Directive   Compliant with Exemptions

China Rohs Regulation   [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure   [Product Environmental Profile](#)

Circularity Profile   [End of Life Information](#)