

Product data sheet

Specifications



Galaxy VM 225 kVA UPS Single 480-480 V, 65kAIC, Start up 5x8

GVMSB225KG65S

Overview

Presentation	A highly compact, energy efficient, 65kAIC rated 3-phase UPS for data centers, facility and industrial applications.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	480 V 3 phases
Main Output Voltage	480 V 3 phases
Rated Power In W	202.5 kW
Rated Power In Va	225 kVA
Output Connector Type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1
Battery Type	External battery system
Provided Equipment	Dust filter Installation guide Integrated network management Seismic compliance Start-up service Top and bottom cable entry

Batteries & Runtime

Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Voltage	480 V
Discharge Battery Voltage	384 V
Maximum Short-Circuit Current	65 kA
Max Current Discharge	549 A
Battery Design Life	5...10 year(s)
Battery Power In Vah	0 VAh runtime
Battery Life	7...10 year(s)
Battery Graph Comments	Estimated runtimes based on battery vendor data, at typical environmental conditions, with no electrical input and balanced PF = 0.9 output.
Extended Runtime	0

General

Bypass Voltage Tolerance	+/- 10 % settable from +/- 4/6/8 and 10 %
--------------------------	---

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Max Bypass Input Current	350 A
Bypass Current Protection	400 A
Redundant	No

Physical

Colour	White
Height	197 cm
Width	100.2 cm
Depth	85.4 cm
Net Weight	704 kg
Usb Compatible	No

Input

Network Frequency	40...70 Hz
Number Of Input Connectors	1 hard wire 3-wire (3P + E)
Input Voltage Limits	360...576 V adjustable 480 V 360...576 V 480 V
Maximum Input Current	347 A
Switching Current Capacity	600 A
Max Short Time Withstand Current	65 kA
Input Harmonic Distortion	Less than 3 % for full load
Input Protection Type	3-pole circuit breaker
Inrush Current	200 A peak
Load Power Factor	0.5 leading to 0.5 lagging
Input Power Factor At Full Load	1

Output

Maximum Configurable Power In W	202.5 kW
Harmonic Distortion	Less than 2 %
Output Frequency	50/60 Hz +/- 1 Hz sync to mains 50/60 Hz +/- 1 Hz unsynchronised
Crest Factor	Unlimited
Wave Type	Sine wave
Output Voltage Tolerance	+/- 1% static and +/- 3% at 100% load step
Output Harmonic Distortion	< 2% linear load and < 3% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Neutral Output Current	244 A
Bypass Type	Built-in static bypass
Efficiency	95.5 % (in battery operation)
Maximum Configurable Power In Va	225 kVA

Conformance

Product Certifications	cUL listed ENERGY STAR V2.0 (USA) FCC part 15 class A UL 1778
Standards	EN/IEC 62040-3 IBC 2012 and CBC2013 to Sds=2.02g OSHDP

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...14999.82 m
Acoustic Level	65 dBA
Heat Dissipation	27670 Btu/h
Ip Degree Of Protection	IP20

Communications & Management

Free Slots	2
Control Panel	7" touch screen display
Emergency Power Off	Optional

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	215.6 cm
Package 1 Width	106 cm
Package 1 Length	149 cm
Package 1 Weight	745 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Environmental Certifications

✓ Energy Star® ENERGY STAR UPS V2.0 (USA)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov