

# Product data sheet

Specifications



## Galaxy VM System Bypass Cabinet 675K 480V

GVMSBC675KG

### Overview

Presentation	System bypass cabinet for use in a parallel configuration with up to a 675kVA maximum load capacity.
Lead Time	Usually Ships within 2 Weeks

### Main

Main Input Voltage	480 V 3 phases
Main Output Voltage	480 V 3 phases
Output Connector Type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1
Provided Equipment	Installation guide

### Physical

Colour	White
Height	197 cm
Width	150.5 cm
Depth	83.7 cm
Net Weight	505 kg
Mounting Support	Floor
Usb Compatible	No

### Input

Network Frequency	50/60 Hz
-------------------	----------

### Conformance

Standards	EN/IEC 62040-3 FCC part 15 class A FCC part 15 class B OSHPD UL 1778
Product Certifications	cUL listed

### Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Storage	-25...55 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...14999.82 m

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	204.6 cm
Package 1 Width	115.6 cm
Package 1 Length	180.5 cm
Package 1 Weight	580.14 kg

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Energy Efficient   Take-back   Transparency

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Rohs Exemption Information   [Yes](#)

Eu Rohs Directive   Compliant with Exemptions

China Rohs Regulation   [China RoHS declaration](#)  
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure   [Product Environmental Profile](#)

Circularity Profile   [End of Life Information](#)