

Product data sheet

Specifications



Galaxy VM System Bypass Cabinet 675K 480V with load bank breaker

GVMSBCLB675KG

Overview

Presentation	System bypass cabinet used in a parallel configuration with a maximum load capacity of 675 kVA. Load bank breaker is included.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	480 V 3 phases
Main Output Voltage	480 V 3 phases
Output Connector Type	Hard wire 4-wire (3P + E) 1 Hard wire 5-wire (3P + N + E) 1
Provided Equipment	Installation guide

Physical

Colour	White
Height	197 cm
Width	178.5 cm
Depth	83.7 cm
Net Weight	585 kg

Input

Network Frequency	40...70 Hz
-------------------	------------

Conformance

Standards	EN/IEC 62040-3 FCC part 15 class A FCC part 15 class B OSHPD UL 1778
-----------	--

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Ambient Air Temperature For Storage	-25...55 °C
Storage Relative Humidity	0...95 %
Storage Altitude	0.00...14999.82 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	204.6 cm
Package 1 Width	115.6 cm
Package 1 Length	208.5 cm
Package 1 Weight	675 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Rohs Exemption Information [Yes](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)
Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)