

Product data sheet

Specifications



APC Easy UPS, 500VA, Floor/Wall Mount, 230V, 6x IEC C13 outlets, AVR

BV500I

Overview

Lead Time	Usually in Stock
-----------	------------------

Main

Main Input Voltage	230 V
Main Output Voltage	230 V
Rated Power In W	300 W
Rated Power In Va	500 VA
Product Or Component Type	Uninterruptible power supply (UPS)
Input Connection Type	IEC 60320 C14
Output Connection Type	6 IEC 60320 C13
Cable Length	1.50 m
Number Of Cables	1
Battery Type	Lead-acid battery
Provided Equipment	User manual

Batteries & Runtime

Efficiency	View Efficiency Graph
Number Of Battery Filled Slots	0
Number Of Battery Free Slots	0
Battery Recharge Time	8 h
Battery Voltage	12 V
Battery Capacity	4.5 Ah
Battery Life	3...5 year(s)
Extended Runtime	0

General

Number Of Power Module Free Slots	0
Number Of Power Module Filled Slots	0
Redundant	No
Ups Size	WS

Physical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	Black
Height	9.25 cm
Width	16.05 cm
Depth	30.5 cm
Net Weight	3.9 kg
Mounting Preference	No preference
Mounting Mode	Not rack-mountable
Two Post Mountable	0
Usb Compatible	No

Input

Network Frequency	50/60 Hz +/- 5 Hz auto-sensing
Input Voltage Limits	170...280 V

Output

Maximum Configurable Power In W	300 W
Output Frequency	50/60 Hz +/- 1 Hz unsynchronised
Ups Type	Line interactive
Wave Type	Stepped approximation to a sinewave
Graph Display	1
Maximum Configurable Power In Va	500 VA
Transfer Time	6 ms typical : 10 ms maximum

Conformance

Product Certifications	CE
Standards	EN/IEC 62040-1:2019/A11:2021 EN/IEC 62040-2:2006/AC:2006 EN/IEC 62040-2:2018

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...90 %
Operating Altitude	0...6667 ft
Ambient Air Temperature For Storage	-20...50 °C
Storage Relative Humidity	0...90 %
Storage Altitude	0.00...15240.00 m
Acoustic Level	40 dBA
Ip Degree Of Protection	IP20

Communications & Management

Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
-------	--

Surge Protection and Filtering

Surge Energy Rate	156 J
-------------------	-------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	23.7 cm
Package 1 Width	37.3 cm
Package 1 Length	14.3 cm
Package 1 Weight	4.2 kg
Scc14	10731304338267

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)