

Product data sheet

Specifications



Galaxy VS UPS 40kW 208V with N+1 power module for external batteries, Start-up 5x8

GVSUPS40KRFS

Overview

Presentation	Highly efficient, easy-to-deploy 40kW, 208V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. Includes 5x8 start-up service and one additional power module for N+1 redundancy.
Lead Time	Usually Ships within 2 Weeks

Main

Main Input Voltage	208 V 3 phases
Other Input Voltage	200 V 220 V
Main Output Voltage	208 V 3 phases
Rated Power In W	40 kW
Rated Power In Va	40 kVA
Battery Type	External battery system Li-Ion (Lithium-Ion) VRLA
Provided Equipment	Dust filter EcoStruxure IT ready (UPS) Installation guide Integrated network management Power modules ship installed Start-up service

Batteries & Runtime

Battery Voltage	384...480 V DC
Discharge Battery Voltage	307 V DC
Max Current Discharge	136 A

General

Bypass Voltage Tolerance	+/- 10 %
Redundant	Yes
Product Or Component Type	Uninterruptible power supply (UPS)

Physical

Colour	White
Height	148.5 cm
Width	52.1 cm
Depth	84.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Net Weight	290 kg
------------	--------

Input

Network Frequency	40...70 Hz
Input Voltage Limits	177...239 V 208 V
Maximum Input Current	143 A
Max Short Time Withstand Current	65 kA
Input Harmonic Distortion	Less than 3 % for full load
Load Power Factor	From 0.7 leading to 0.7 lagging without any derating

Output

Maximum Configurable Power In W	40 kW
Output Frequency	50 Hz sync to mains 60 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised 60 Hz +/- 0.1 % for 60 Hz nominal unsynchronised
Crest Factor	2.5
Wave Type	Sine wave
Output Voltage Tolerance	+/-1% after 50ms
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Bypass Type	Built-in static bypass
Maximum Configurable Power In Va	40 kVA

Conformance

Standards	IEC 62040-1-1 IEC 62040-2 UL 1778 5th edition FCC part 15 class A IEC 60721-4-2 level 2M2 UL 924
-----------	---

Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3300 ft
Ambient Air Temperature For Storage	-25...55 °C
Storage Relative Humidity	10...80 % non-condensing
Acoustic Level	68 dBA
Heat Dissipation	7756 Btu/h
Ip Degree Of Protection	IP21

Communications & Management

Control Panel	Touch screen LCD user interface
---------------	---------------------------------

Packing Units

Unit Type Of Package 1	PCE
------------------------	-----

Number Of Units In Package 1	1
Package 1 Height	168 cm
Package 1 Width	64 cm
Package 1 Length	99 cm
Package 1 Weight	250 kg

Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient Take-back Transparency RoHS/REACH

Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant with Exemptions

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile [End of Life Information](#)