

# Product data sheet

Specifications



## Acti9 - MINp - silent electronic timer - adjustable from 0.5 to 60 minutes

CCT15233

### Main

Range Of Product	Acti9
Product Name	Acti9 MIN
Device Short Name	MINp
Product Or Component Type	Silent electronic timer
Product Compatibility	Mechanical compatibility with electrical comb busbars
Function Available	Switch-off warning
Colour Tint	White (RAL 9003)

### Complementary

Device Application	Building
Load Type	Fluocompact lampconventional ballast 1500 VA Fluorescent lamp 22 x electronic ballast 23 W 230 V AC halogen lamp 3600 W 230 V AC incandescent lamp 3600 W Fluorescent lamp 24 x electronic ballast 15 W Fluorescent lamp 27 x electronic ballast 11 W Fluorescent lamp 34 x electronic ballast 7 W Dual mounted fluorescent tubeconventional ballast 3600 VA Fluorescent tubeelectronic ballast 1000 VA Non-corrected fluorescent tubeconventional ballast 3600 VA Parallel-corrected fluorescent tubeconventional ballast 1200 VA Serial-corrected fluorescent tubeconventional ballast 3600 VA
Power Consumption In Va	6 VA
Maximum Switching Current	16 A - 230 V AC pf = 1
[Ue] Rated Operational Voltage	230 V AC +10 % -15 % at 50/60 Hz
Time Delay	Adjustable from 0.5 to 20 minutes
Mounting Support	DIN rail
9 Mm Pitches	2
Connections - Terminals	Screw terminals - <= 6 mm²
Electrical Insulation Class	Class II
Width	18 mm
Height	89 mm
Depth	66 mm
Net Weight	103 g

### Environment

Ambient Air Temperature For Operation	-25...50 °C
---------------------------------------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ip Degree Of Protection	IP20 B
-------------------------	--------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.2 cm
Package 1 Width	7.0 cm
Package 1 Length	10.0 cm
Package 1 Weight	100.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	130
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	13.877 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>