

Product data sheet

Specifications



STD - DIN - remote control dimmer - 400 W

CCTDD20001

Main

| | |
|---------------------------|-------------------------------|
| Range Of Product | Acti9 |
| Product Name | Acti9 STD |
| Product Or Component Type | Remote control dimmer |
| Device Short Name | STD |
| Product Compatibility | Power regulators designed |
| Function Available | Automatic load type detection |

Complementary

| | |
|--------------------------------|--|
| Device Application | Building |
| Load Type | 230 V AC halogen lamp: 40...400 W 230 V AC incandescent lamp: 40...400 W low voltage halogen lamp with electronic transformer: 40...400 W motor: 40...200 W low voltage halogen lamp with conventional transformer: 40...400 W low voltage halogen lamp with toroidal transformer: 40...300 W |
| Control Type | Local control: push-button Remote control: push-button |
| Power Consumption In Va | 0.8 VA |
| Thermal Losses | 3 W |
| [Ue] Rated Operational Voltage | 230 V AC +/- 10 % at 50 Hz |
| Protection Type | Electronic overload protection Electronic over temperature protection Electronic overvoltage protection Single shot thermal fuse |
| Mounting Support | DIN rail |
| 9 Mm Pitches | 4 |
| Connected Auxiliaries | Maximum 25 auxiliary push-buttons without light indication, distance : < 50 m Maximum 5 auxiliary push-buttons with light indication, distance : < 50 m |
| Connections - Terminals | Screw terminals, 2 cable(s) 4 mm² top |
| Height | 85 mm |
| Width | 36 mm |
| Depth | 62 mm |
| Net Weight | 80 g |

Environment

| | |
|-------------------------|------|
| Ip Degree Of Protection | IP20 |
|-------------------------|------|

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|---------------------------------------|---|
| Standards | EN 60669-2-1 |
| Directives | 73/23/EEC - low voltage directive 89/336/EEC - electromagnetic compatibility |
| Ambient Air Temperature For Operation | 0...70 °C |
| Ambient Air Temperature For Storage | 0...60 °C |

Packing Units

| | |
|------------------------------|---------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 8.0 cm |
| Package 1 Width | 9.5 cm |
| Package 1 Length | 9.5 cm |
| Package 1 Weight | 137.0 g |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Compliant with Exemptions |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |