

Product data sheet

Specifications



Acti9 - STD400LED DIN universal dimmer

CCTDD20016

Main

Range Of Product	Acti9
Product Name	Acti9 STD
Product Or Component Type	Remote control dimmer
Device Short Name	STD
Function Available	Automatic load type detection

Complementary

Device Application	Building
Load Type	halogen lamp: <= 400 W incandescent lamp: <= 400 W fluocompact lamp, dimmable: <= 80 W LED lamp, dimmable: <= 60 W low voltage halogen lamp with electronic transformer: <= 300 W low voltage halogen lamp with ferromagnetic transformer: <= 400 W
Control Type	Local control: push-button Remote control: push-button
Power Consumption In Va	0.8 VA
Thermal Losses	3 W
[Ue] Rated Operational Voltage	230 V AC - 15...10 % at 50 Hz
Input Voltage	8...230 V AC/DC
Protection Type	Electronic overload protection Electronic over temperature protection
Mounting Support	DIN rail
9 Mm Pitches	2
Connected Auxiliaries	Maximum 10 auxiliary push-buttons without light indication, distance : < 100 m
Dimmer Type	Dimmer with memory
Height	85 mm
Width	18 mm
Depth	60 mm
Net Weight	65 g

Environment

Ip Degree Of Protection	IP20
Standards	EN 60669-2-1 EN 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Directives	2006/95/EC - low voltage directive 2004/108/EC - electromagnetic compatibility
Ambient Air Temperature For Operation	-30...50 °C
Ambient Air Temperature For Storage	-20...70 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.3 cm
Package 1 Width	10.5 cm
Package 1 Length	3.3 cm
Package 1 Weight	104.0 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	86
Package 2 Height	30.0 cm
Package 2 Width	30.0 cm
Package 2 Length	40.0 cm
Package 2 Weight	9.404 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information