

# Product data sheet

Specifications



## Galaxy VS UPS 60kW 400V for up to 5 internal 9Ah smart modular battery strings, Start-up 5x8

GVSUPS60K0B5HS


### Overview

Presentation	Highly efficient, easy-to-deploy 60kW, 400V 3-phase UPS that brings best-in-class power protection and low total cost of ownership to edge, small and medium data centers, as well as to critical infrastructure in commercial and industrial applications. This UPS is for up to 5 smart modular high capacity battery strings, but is supplied without batteries, so you can easily customize the battery runtime. Includes 5x8 start-up service.
Lead Time	Usually Ships within 2 Weeks

### Main

Main Input Voltage	400 V 3 phases
Other Input Voltage	380 V 415 V
Main Output Voltage	400 V 3 phases
Other Output Voltage	380 V 415 V
Rated Power In W	60 kW
Rated Power In Va	60 kVA
Battery Type	Internal modular battery VRLA
Provided Equipment	Dust filter Installation manual Integrated network management Start-up service EcoStruxure Ready

### Batteries & Runtime

Efficiency	<a href="#">View Efficiency Graph</a> 
Battery Voltage	480 V
Discharge Battery Voltage	384 V
Max Current Discharge	163 A
Battery Power In Vah	0 VAh runtime
Extended Runtime	0

### General

Redundant	No
Product Or Component Type	Uninterruptible power supply (UPS)

### Physical

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Colour	White
Height	197 cm
Width	55 cm
Depth	84.7 cm
Net Weight	281 kg
Usb Compatible	No

## Input

Network Frequency	40...70 Hz
Input Voltage Limits	340...460 V 400 V
Maximum Input Current	108 A
Max Short Time Withstand Current	65 kA
Input Harmonic Distortion	Less than 3 % for full load
Load Power Factor	From 0.7 leading to 0.7 lagging without any derating
Input Power Factor At Full Load	0.99

## Output

Maximum Configurable Power In W	60 kW
Harmonic Distortion	Less than 3 %
Output Frequency	50 Hz sync to mains 60 Hz sync to mains
Crest Factor	2.5
Wave Type	Sine wave
Output Voltage Tolerance	+/- 5% after 2ms +/-1% after 50ms
Output Harmonic Distortion	< 1% linear load and < 3% non-linear load
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Bypass Type	Built-in static bypass
Maximum Configurable Power In Va	60 kVA

## Conformance

Standards	IEC 62040-1-1 IEC 62040-2 OSHDP
-----------	---------------------------------------

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 % non-condensing
Operating Altitude	0...3300 ft
Ambient Air Temperature For Storage	-15...40 °C
Storage Relative Humidity	10...80 % non-condensing
Storage Altitude	0.00...3048.00 m
Acoustic Level	54 dBA

Heat Dissipation	7103 Btu/h
Ip Degree Of Protection	IP20

## Communications & Management

Control Panel	Touch screen LCD user interface
---------------	---------------------------------

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	208.2 cm
Package 1 Width	101 cm
Package 1 Length	75.5 cm
Package 1 Weight	250 kg

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Energy Efficient   Take-back   Transparency   RoHS/REACH

## Resource performance

✓ Energy Efficient Product

✓ Take-Back Program Available

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation   [REACH Declaration](#)

Eu Rohs Directive   Compliant with Exemptions

China Rohs Regulation   [China RoHS declaration](#)

Environmental Disclosure   [Product Environmental Profile](#)

Circularity Profile   [End of Life Information](#)