



# Product data sheet

Specifications

## In/Outdoor Non-Armoured Cable, Multi-Mode, 6 Core, 62.5um, LSZH



DFXAI62GLH06

 **Discontinued on:** Dec 31, 2018

 **Discontinued**

### Main

Range Of Product	Digilink
Product Or Component Type	Fibre optic cable multi mode
Optic Fibre Type	Non armoured (indoor/outdoor)

### Complementary

Optic Fiber Core	62.5 µm
Condition Of Use	Indoor/outdoor
Cable Weight	90 kg / 1 km
Bending Radius	20 x overall diameter
Number Of Optic Fibre	6
Tensile Strength	2670 N
Crush Resistance	0.044 N/m

### Environment

Ambient Air Temperature For Operation	-30...70 °C
Ambient Air Temperature For Storage	-40...75 °C
Standards	TIA/EIA-568-B ISO/IEC 11801

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)

## Well-being performance

 Toxic Heavy Metal Free

 Mercury Free

 Rohs Exemption Information [Yes](#)

<b>Eu Rohs Directive</b>	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
--------------------------	---

<b>China Rohs Regulation</b>	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
------------------------------	---

<b>Circularity Profile</b>	No need of specific recycling operations
----------------------------	--