

# Product data sheet

Specifications



## 1 Gang 2 Way Horizontal Dolly Switch with Blue LED, Grey Silver

E3031H2\_EBGS

### Main

Range	Neo
Wiring device mounting	Surface Flush
Switch function	2-way
Switch application	Switch
Load type	Resistive Fluorescent lamp Incandescent lamp Inductive
Bulb type	LED (blue)
Colour tint	Grey silver

### Complementary

Rated current	10 A at 250 V AC 50/60 Hz
Number of gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	3 x 2.5 mm <sup>2</sup> for solid cable(s) 3 x 2.5 mm <sup>2</sup> for stranded cable(s) 4 x 1.5 mm <sup>2</sup> for solid cable(s) 4 x 1.5 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	23.5 mm
Depth	36 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	IEC 60669-1 GB 16915.1 EN 60669-1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.6 cm
Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	68 g
Unit Type of Package 2	BB1
Number of Units in Package 2	8
Package 2 Height	15 cm
Package 2 Width	19 cm
Package 2 Length	8 cm
Package 2 Weight	558 g
Unit Type of Package 3	CAR
Number of Units in Package 3	80
Package 3 Height	21 cm
Package 3 Width	31 cm
Package 3 Length	50 cm
Package 3 Weight	6580 g

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)