

# Product data sheet

Specifications



## Galaxy VX 800kVA, 400V, Start up 5x8

GVX800K800NHS

### Overview

Presentation	A highly efficient, modular, 800 kVA 3-phase UPS that provides the performance, flexibility, and maximized asset utilization today's large data centers and mission critical applications require. This EcoStruxure connected UPS features up to 99% efficiency in eConversion mode. Includes 5x8 start-up service.
Lead Time	Special Order - Call for Quoted Lead Times

### Main

Main Input Voltage	400 V 3 phases
Main Output Voltage	400 V 3 phases
Rated Power In W	800 kW
Rated Power In Va	800 kVA
Battery Type	External battery system
Provided Equipment	Installation guide Start-up service

### Batteries & Runtime

Battery Voltage	480 V
Discharge Battery Voltage	384 V DC
Battery Power In Vah	0 VAh runtime
Extended Runtime	0

### General

Redundant	No
-----------	----

### Physical

Colour	White
Width	360 cm
Net Weight	3110 kg
Usb Compatible	No

### Input

Network Frequency	40...70 Hz
Maximum Input Current	1361 A
Load Power Factor	From 0.7 leading to 0.5 lagging without any derating

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Output

Maximum Configurable Power In W	800 kW
Output Frequency	50 Hz sync to mains 60 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
Crest Factor	3 with THC <5%
Wave Type	Sine wave
Output Overload Operation	10 minutes at 125% and 60 seconds at 150%
Maximum Configurable Power In Va	800 kVA

## Conformance

Product Certifications	C-Tick CE
Standards	EN/IEC 62040-1 EN/IEC 62040-2 EN/IEC 62040-3 IBC 2012 IEC 62040-4 ISTA 2B

## Environmental

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Operating Altitude	0...3333 ft
Storage Relative Humidity	0...95 % non-condensing
Acoustic Level	69.5 dB
Heat Dissipation	128620 Btu/h
Ip Degree Of Protection	IP20

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.01 kg

## Contractual warranty

Warranty	1 year on-site repair or replace with factory authorized Start-Up
----------	---

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.


[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency

## Well-being performance

 Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins