

# Product data sheet

Specifications



## 20A Horizontal Dolly Double Pole Switch with White LED, White

E3031HD20\_EWWW

### Main

Range	Neo
Product or component type	Control switch
Device application	Control
Wiring device mounting	Flush Surface
Switch function	2-pole
Switch application	Switch
Load type	Resistive Inductive Fluorescent lamp
Bulb type	LED (white)
Colour tint	White

### Complementary

Rated current	20 AX at 250 V AC 50/60 Hz
Number of gangs	1 gang horizontal
Material	Brass: metal parts Polycarbonate: plastic part Steel: metal parts
Clamping connection capacity	1 x 2.5...1 x 6 mm <sup>2</sup> for solid cable(s) 1 x 2.5...1 x 6 mm <sup>2</sup> for stranded cable(s)
Connections - terminals	Pillar terminals
Width	87 mm
Height	87 mm
Embedding depth	19.7 mm
Depth	33.1 mm

### Environment

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Environmental characteristic	Indoor use
Standards	EN 60669-1 GB 16915.1

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Weight	132.325 g
Package 1 Height	21 cm
Package 1 Width	32.5 cm
Package 1 Length	50 cm

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

## Contractual warranty

Warranty	18 months
----------	-----------

## Recommended replacement(s)