

Product data sheet

Specifications



Easy UPS 3S 20 kVA 400 V 3:1 UPS for external batteries

E3SUPS20K3I

Overview

| | |
|--------------|--|
| Presentation | High-efficiency 3-phase UPS that features advanced product features, competitive specifications, and robust electrical design, making business continuity easy in the data center or electrical room. This is an exceptionally easy to install, operate, maintain, and service 20 kVA UPS, ideal for small and medium businesses. Includes dust filter and conformance-coated boards for harsh environments. This UPS is supplied without batteries, so you can easily customize the battery solution. |
| Lead Time | Usually Ships within 6 Weeks |

Main

| | |
|---------------------------|------------------------------------|
| Main Input Voltage | 400 V 3 phases |
| Product Or Component Type | Uninterruptible power supply (UPS) |
| Other Input Voltage | 380 V 415 V |
| Main Output Voltage | 230 V |
| Other Output Voltage | 220 V 240 V |
| Rated Power In W | 20 kW |
| Rated Power In Va | 20 kVA |
| Provided Equipment | Dust filter Installation guide |

Batteries & Runtime

| | |
|--------------------------------|---------------------------------------|
| Efficiency | View Efficiency Graph |
| Battery Type | External battery system |
| Maximum Short-Circuit Current | 10 kA |
| Number Of Battery Filled Slots | 0 |
| Number Of Battery Free Slots | 0 |

Physical

| | |
|----------------|------------------|
| Colour | White (RAL 9003) |
| Height | 77 cm |
| Width | 25 cm |
| Depth | 80 cm |
| Net Weight | 58 kg |
| Usb Compatible | Yes |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Input

| | |
|---------------------------------|-------------|
| Maximum Input Current | 37 A |
| Input Power Factor At Full Load | 0.99 |
| Input Voltage Limits | 304...477 V |
| Network Frequency | 45...65 Hz |

Output

| | |
|----------------------------------|--|
| Maximum Configurable Power In Va | 20 kVA |
| Maximum Configurable Power In W | 20 kW |
| Output Frequency | 50 Hz sync to mains 60 Hz sync to mains |
| Harmonic Distortion | Less than 3 % |
| Output Overload Operation | 10 minutes at 125% and 60 seconds at 150% |
| Ups Type | Double conversion online |
| Crest Factor | 3 : 1 |

Conformance

| | |
|------------------------|------------------|
| Product Certifications | CE EAC RCM |
|------------------------|------------------|

Environmental

| | |
|---------------------------------------|-------------------------|
| Ambient Air Temperature For Operation | 0...40 °C |
| Relative Humidity | 0...95 % non-condensing |
| Operating Altitude | 0...3281 ft |
| Ambient Air Temperature For Storage | -15...40 °C |
| Storage Relative Humidity | 0...95 % non-condensing |
| Storage Altitude | 0.00...15240.00 m |
| Acoustic Level | 60 dBA |
| Heat Dissipation | 870 W |
| Ip Degree Of Protection | IP20 |

Packing Units

| | |
|------------------------------|----------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 101.5 cm |
| Package 1 Width | 98.2 cm |
| Package 1 Length | 40 cm |
| Package 1 Weight | 75 kg |

Contractual warranty

| | |
|----------|---|
| Warranty | 1 year on-site repair or replace with factory authorized Start-Up |
|----------|---|

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) |
| China Rohs Regulation | China RoHS declaration Product out of China RoHS scope. Substance declaration for your information |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | End of Life Information |