

# Product data sheet

Specifications



## 13A 250V TWIN SOCKET OUTLET

ET3426\_WW\_G19

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	Neo
Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	3P with shutters
Outlet Standard	MS 589 SS 145 BS 1363
Colour Tint	White

### Complementary

Wiring Device Mounting	Surface Flush
Rated Current	13 A at 250 V AC 50/60 Hz
Material	Brass: contact Nylon: shutter Polycarbonate: grid plate Polycarbonate: surround Steel with brass plating: screws Steel with brass plating: terminals
Connections - Terminals	Pillar terminals
Width	147 mm
Height	87 mm
Depth	17.5 mm

### Environment

Ambient Air Temperature For Operation	0...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	Indoor use
Standards	BS 1363 MS 589 SS 145

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	14.7 cm
Package 1 Width	8.7 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	1.75 cm
Package 1 Weight	0.001 g

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations