


Product data sheet

Specifications



Ultra - adjustable internal corner - 70 x 20 mm - ABS - DIY - 2 pack

ETK70220D

 **Discontinued on:** Dec 17, 2020

 **Discontinued**

Main

Range Of Product	Ultra
Product Or Component Type	Internal corner
Device Application	Cable distribution
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 2

Complementary

Trunking Dimension	70 x 20 mm
Trunking Material	Plastic
Adjustment	Adjustable
Fixing Mode	Snap-fitted
Material	ABS thermoplastic enclosure
Height	74 mm
Width	50 mm
Depth	50 mm

Environment

Product Certifications	low voltage directive 2006/95/EC
Standards	EN 50085-1:2005 EN 50085-2-1:2006
Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.4 cm
Package 1 Width	5 cm
Package 1 Length	5 cm
Package 1 Weight	17 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations