

Product data sheet

Specifications



Thorsman Digital Clamp Test Meter

IMT23214

Main

Range	Thorsman
Product Or Component Type	Test meter
Supply	2 battery 3 V

Complementary

Display Digits	3.5
Type Of Setting	Automatic reset
Signaling Function	Low battery by visual
Function Available	Audible continuity High precision measuring Tactile barrier for safety Data hold function
Type Of Measurement	Voltage DC: 200mV/2/20/200/600 V Resistance: 200 Ohm/2/20/200 kOhm/20 MOhm Voltage AC: 2/20/200/600 V Current AC: 2/20/200/600 A Continuity: < 30 Ohm Diode check: 1.5 V
Measurement Category	Category III 600 V
User Language	Spanish Hungarian German Portuguese French Polish
Height	190 mm
Width	76 mm
Depth	36 mm
Product Weight	160 g with battery

Environment

Standards	IEC 61010
-----------	-----------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	16 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Length	29.1 cm
Package 1 Weight	314 g
Unit Type Of Package 2	S03
Number Of Units In Package 2	10
Package 2 Height	30 cm
Package 2 Width	30 cm
Package 2 Length	40 cm
Package 2 Weight	4 kg

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Sustainable Packaging

Resource performance

✔ Sustainable Packaging

Well-being performance

✔ Reach Free Of Svhc

✔ Toxic Heavy Metal Free

✔ Mercury Free

✔ Rohs Exemption Information Yes

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)