

Product data sheet

Specifications



Miniature circuit breaker (MCB), Easy9, 2P, 10A, C curve, 6000A (IEC/EN 60898-1)

EZ9F56210

Main

Range	Easy9
Device Application	Distribution
Product Or Component Type	Miniature circuit-breaker
Device Short Name	Easy9 MCB
Poles	2P
Number Of Protected Poles	2
[In] Rated Current	10 A
Network Type	AC
Trip Unit Technology	Thermal-magnetic
Curve Code	C
Breaking Capacity	10000 A Icn at 220 V AC 50/60 Hz conforming to IEC 60898-1 6000 A Icn at 400 V AC 50/60 Hz conforming to IEC 60898-1
Suitability For Isolation	Yes conforming to IEC 60898-1

Complementary

Network Frequency	50/60 Hz
[Ue] Rated Operational Voltage	220 V AC 50/60 Hz 400 V AC 50/60 Hz
Magnetic Tripping Limit	5...10 x In
[Ics] Rated Service Breaking Capacity	6 kA 100 % x Icn at 230 V AC 50/60 Hz conforming to IEC 60898-1
[Ui] Rated Insulation Voltage	500 V AC 50/60 Hz conforming to IEC 60898-1
[Uimp] Rated Impulse Withstand Voltage	4 kV conforming to IEC 60898-1
Contact Position Indicator	Yes
Control Type	Toggle
Local Signalling	Without
Mounting Mode	Clip-on
Mounting Support	DIN rail
9 Mm Pitches	4
Height	81 mm
Width	36 mm
Depth	66.5 mm
Colour	Grey (RAL 7035)

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Mechanical Durability	10000 cycles
Electrical Durability	4000 cycles
Connections - Terminals	Tunnel type terminal (top or bottom) 1...25 mm² rigid Tunnel type terminal (top or bottom) 1...16 mm² flexible
Tightening Torque	2 N.m top or bottom
Earth-Leakage Protection	Without

Environment

Standards	IEC 60898-1
Product Certifications	CE
Ip Degree Of Protection	IP20 conforming to IEC 60529
Pollution Degree	2
Tropicalisation	2
Relative Humidity	95 % at -5...60 °C
Ambient Air Temperature For Operation	-5...60 °C
Ambient Air Temperature For Storage	-40...85 °C

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	7.6 cm
Package 1 Width	3.6 cm
Package 1 Length	8.5 cm
Package 1 Weight	205 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	6
Package 2 Height	7.6 cm
Package 2 Width	9 cm
Package 2 Length	22.6 cm
Package 2 Weight	1.292 kg
Unit Type Of Package 3	S03
Number Of Units In Package 3	72
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	14.76 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance



Mercury Free



RoHS Exemption Information

Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu RoHS Directive

Compliant with Exemptions

China RoHS Regulation

[China RoHS declaration](#)

Product out of China RoHS scope. Substance declaration for your information

Environmental Disclosure

[Product Environmental Profile](#)

Weee

The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Circularity Profile

No need of specific recycling operations