

# Product data sheet

Specifications



## Thorsman - TEX-C3 M8x50 - through bolt - set of 100

IMT38015

 **Discontinued on:** Jan 3, 2022

 **Discontinued**

**Important message:** This product belongs to Cable Support which is no longer commercialized by Schneider Electric. As per the first of January 2022 the commercialization is managed by Wibe-Group, Please follow the link [www.wibe-group.com](http://www.wibe-group.com) for further details.

### Main

Range Of Product	Thorsman
Product Or Component Type	Through bolt
Device Short Name	TEX
Provided Equipment	Nut Washer
Quantity Per Set	Set of 100

### Complementary

Mounting Support	Natural rock Concrete
Type Of Installation	Indoor/outdoor
Thread Type	M8
Screw Length	50 mm
Drilling Diameter	8 mm
Minimum Drilling Depth	48 mm
Thickness	Fixture: 0...5 mm
Embedding Depth	35 mm
Tightening Torque	23 N.m
Material	Steel hot-dip zinc
Atmospheric-Corrosivity Category	C3
Practical Load Capacity	Pull-out load: 3.4 kN for concrete C20/C25 Shear: 4.8 kN for concrete C20/C25
Serviceability Limit State	Pull-out load: 870 kg for concrete C20/C25
Ultimate Limit State	Pull-out load: (safety cl 1)450 kg for concrete C20/C25 Shear: (safety cl 1)640 kg for concrete C20/C25 Pull-out load: (safety cl 2)410 kg for concrete C20/C25 Shear: (safety cl 2)580 kg for concrete C20/C25
Accidental Action	Pull-out load: 900 kg for concrete C20/C25 Shear: 1270 kg for concrete C20/C25

### Environment

Ambient Air Temperature For Operation	-20...60 °C
---------------------------------------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	0.8 cm
Package 1 Width	0.8 cm
Package 1 Length	5 cm
Package 1 Weight	23 g

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



## Transparency

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations