

Product data sheet

Specifications

Mureva Tube GT HF - bend - diam. 20 - black - IP30



IMT49020

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range Of Product	Mureva
Product Or Component Type	Bend
Mounting Location	Indoor Outdoor
Nominal Cross Section	177 mm²
Diameter	External: 20 mm Internal: 15 mm
Colour Tint	Black (RAL 9005)

Complementary

Quantity Per Set	25 pieces
Ambient Air Temperature For Operation	-25...95 °C
Material	PC/ABS
Standards	IEC 61386

Environment

Ip Degree Of Protection	IP30
Ik Degree Of Protection	IK07
Environmental Characteristic	Non-flame propagating

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.2 cm
Package 1 Width	17 cm
Package 1 Length	29.2 cm
Package 1 Weight	0.001 g

Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information [Yes](#)

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations