

Product data sheet

Specifications



CYB - double USB charger 2.4 A - white

INS60522

Main

Range	CYB
Product Or Component Type	USB charger

Complementary

Device Application	Charger
Device Mounting	Flush
Device Presentation	Mechanism with central plate
Colour Tint	White
Surface Treatment	Untreated
Fixing Mode	By screws By claws
Type Of Packing	Flow-pack
[Ue] Rated Operational Voltage	100...240 V AC +/- 10 % at 50/60 Hz
Power Consumption In W	0.075 W
Nominal Output Power	12 W
Input Power	12 W
Service Life In Hours	30000 h 12 W
Integrated Connection Type	1 USB type A 5 V DC, maximum load current: 2.4 A 1 USB type C 5 V DC
Material	ABS (acrylonitrile butadiene-styrene): centre plate PC (polycarbonate) GF10 FR: casing PC (polycarbonate) GF10 FR: internal cover
Protection Type	Short-circuit protection
Number Of Terminals	2 screw terminals
Clamping Connection Capacity	2 x 0.75...2 x 2.5 mm ² for rigid cable(s) 2 x 0.75...2 x 2.5 mm ² for flexible cable(s) 2 x 0.75...2 x 2.5 mm ² for stranded cable(s)
Wire Stripping Length	8 mm
Product Compatibility	Mobile/tablet Mac iOS Mobile/tablet Android Mobile/tablet Windows
Height	45 mm
Width	22.5 mm
Depth	42 mm
Embedding Depth	30.8 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environment

Ambient Air Temperature For Operation	0...40 °C
Ambient Air Temperature For Storage	-5...50 °C
Standards	EN 62684 ETSI EN 301 489-4 EN 60950-1
Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive
Electrical Insulation Class	Class II
Ik Degree Of Protection	IK04
Ip Degree Of Protection	IP20

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	6.5 cm
Package 1 Width	8.5 cm
Package 1 Length	8.5 cm
Package 1 Weight	137.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	9.4 cm
Package 2 Width	38.5 cm
Package 2 Length	18.8 cm
Package 2 Weight	1.51 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	30
Package 3 Height	18.5 cm
Package 3 Width	30.0 cm
Package 3 Length	40.0 cm
Package 3 Weight	4.94 kg

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins